
MEDIUM BASE LAMPHOLDER

10085 | [Pass & Seymour](#)



FEATURES & BENEFITS

Medium base, porcelain, keyless, single circuit with 2-18 awg leads 6" long. White.



- Quality Materials.
- Durability.
- Time-tested design.

SPECIFICATIONS

GENERAL INFO

Type: Incandescent Medium Base Lampholder

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: Yes
CUL Listing No: No
cULus: No
cURus: No
Federal Spec: No
UL Listing No: Yes
UN SPSC: 39111803
UR: No

DIMENSIONS

Diameter (US): 1.40"
Height (US): 2.00"

TECHNICAL INFORMATION

Volts: 250V
Volts (AC): 250
Watts: 660

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA
Buy American Act Status: No

MEDIUM BASE LAMPHOLDER

10085 | [Pass & Seymour](#)



FEATURES & BENEFITS

Medium base, porcelain, keyless, single circuit with 2-18 awg leads 6" long. White.



- Quality Materials.
- Durability.
- Time-tested design.

SPECIFICATIONS

GENERAL INFO

Type: Incandescent Medium Base Lampholder

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: Yes
CUL Listing No: No
cULus: No
cURus: No
Federal Spec: No
UL Listing No: Yes
UN SPSC: 39111803
UR: No

DIMENSIONS

Diameter (US): 1.40"
Height (US): 2.00"

TECHNICAL INFORMATION

Volts: 250V
Volts (AC): 250
Watts: 660

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA
Buy American Act Status: No