

PRODUCT INFORMATION

Flush

Intended Use

Provides general illumination in residential and light commercial applications. Ideal for use in foyers, hallways, bedrooms, offices, utility work areas, stairways and many other rooms in the house.

Construction

The Disk emphasizes contemporary design to complement

decors with a modern sensibility. A polished brushed nickel, low-profile housing and a flat glass diffuser make a subtle but bold statement. The diffuser has a frosted, white screened center that provides a widespread, even illumination. Its clear outer ring has a glowing effect when illuminated which is complemented by a flat polished brushed nickel disk finial. Can be wall mounted.

The finial provides easy access for cleaning and maintenance.

Electrical

Includes (1) 22W or (1) 40W circline T5 3500K fluorescent lamp for energy efficiency, superior color rendering and long life.

Residential electronic ballast (120V, 60Hz) ensures no flickering and quiet operation without interfering with other home electronics.

Use with non-dimmable switches only.

Installation

All mounting hardware included.

Listings

CUL Listed to U.S. and Canadian safety standards and suitable for damp locations. ENERGY STAR® qualified. ADA compliant.

DISK



ADA



ORDERING INFORMATION

Example: 11560 BNP


Series ¹	Ballast ²	Finish	Options
11560 11" diameter, (1) 22W circline T5 lamp	(blank) 120V residential electronic ballast (standard)	BNP Polished brushed nickel	Consult factory.
11562 15" diameter, (1) 40W circline T5 lamp	For other voltage and ballast, consult factory.		

ADDITIONAL INFORMATION

For additional product information, visit www.lightahome.com.

ACCESSORIES/REPLACEMENT PARTS	
FC22T35	22W circline T5 fluorescent 3500K lamp
FC40T35	40W circline T5 fluorescent 3500K lamp
DDISK11	11" opal glass diffuser
DDISK15	15" opal glass diffuser

Drawings are for dimensional detail only and may not represent actual mechanical configuration. Dimensions are shown in inches (centimeters) unless otherwise noted.



Notes

- Includes (1) 22W and (1) 32W circline T5 3500K fluorescent lamps.
- Use with non-dimmable switches only.

PRODUCT INFORMATION

Linear Design

Intended Use

Provides general illumination in residential and light commercial applications. Ideal for use in kitchens, offices, utility areas or closets.

Construction

Traditional style fixture with cast ends in a black-bronze or

white finish with matching finials. Durable, milk-white acrylic diffuser provides widespread, uniform illumination. Finials provide easy access and maintenance.

Electrical

Utilizes T8 linear lamp(s) for energy efficiency, superior color rendering and long life (not included).

Residential electronic ballast (120V, 60Hz) ensures no flickering and quiet operation without interfering with other home electronics. Use with non-dimmable switches only.

Installation

All mounting hardware included.

Listings

RE ballast fixtures are UL Listed and CSA Certified (standard), suitable for damp locations and ENERGY STAR® qualified. For non-RE ballast fixtures, UL Listed (standard) and CSA Certified (see Options).

RIGBY



ORDERING INFORMATION


Example: 11642RE BZ

Series/Ballast ^{1,2}	Finish	Lamp type	Voltage	Options
Series¹ 11642 1' x 4', (2) T8 lamps 11644 1-1/2' x 4', (4) T8 lamps For other voltage and ballast, consult factory.	Ballast² RE 120V residential electronic T8 (standard)	RE ballast fixtures only (blank) No specification required Non-RE ballast fixtures only 32 32W T8	RE ballast fixtures only (blank) No specification required Non-RE ballast fixtures only 120 120V 277 277V 347 347V For other voltage, consult factory.	CSA Meets Canadian standards NOM Meets Mexican standards

ADDITIONAL INFORMATION

For additional product information, visit www.lightahome.com.

Drawings are for dimensional detail only and may not represent actual mechanical configuration. Dimensions are shown in inches (centimeters) unless otherwise noted.



Notes

- Lamps not included.
- For use with non-dimmable switches only.