



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



1222I Switch, Hubpro, 2-Pole, 20A 120/277V, Iv *Hubbell Wiring Devices*

Catalog Number	1222I
Manufacturer	Hubbell Wiring Devices
Description	Toggle Switch, 2 Poles, 20 A, 120 to 277 V Ac, Double Pole Contact Configuration, Thermoplastic (Body);Nylon (Toggle) Material, Steel Contact Material, Ivory, Back and Side Wired Connection, Screw Mount, Zinc Plated (Bridge), 1.49 In (L) X 1 In (W) X 4.18 In (H), -40 °C Operating Temperature, +75 °C Operating Temperature, 0.15 LB
Weight per unit	0.0790 (lbs/each)
Product Category	Gen Purpose Switches

Features

action	Positive Snap
amperage rating	20
connection	Back and Side Wired
Contact Rating	Per UL 20
insulation	False
operating cycles	50,000
pallet quantity	4000
Poles	Double Pole
Switch Type	Toggle
Wattage	5540

Dimensions and Weight

Size	4.18 in x 1.49 in x 1.83 in
------	-----------------------------

Descriptions

Description	SWITCH, HUBPRO, 2-POLE, 20A 120/277V, IV
extra long description	HWDK 1222I SWITCH, HUBPRO, 2-POLE,

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585181400
series	Heavy Duty
UPC	783585181400

Taxonomies, Classifications, and Categories

Category Description	Commercial switches
Type	TOGGLE



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.079

Uses, Certifications, and Standards

Enclosure	None
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
standard	UL Listed