

Eaton 1254-BOX

Catalog Number: 1254-BOX

Eaton power device receptacle, #12 - 4 AWG, 50A, Flush, 250V, Back, Black, NEMA 6-50R, Two-pole, Three-wire, Two-pole, three-wire, grounding, Screw, Glass-filled nylon, Power, Used with A42



General specifications

Product Name	Catalog Number
Eaton power device receptacle	1254-BOX
UPC	Product Length/Depth
032664306709	3.88 in
Product Height	Product Width
2.25 in	2.94 in
Product Weight	Compliances
0.35 lb	RoHS Compliant NAFTA
Certifications	
CSA Certified UL Listed	

Product specifications

Used with

A42

Amperage Rating

50 A

Voltage rating

250 V

Wiring method

Back

Number of wires

3

Mounting method

Flush

Number Of Poles

Two-pole

Color

Black

Connection type

Screw

Style

Power

Allowable wire size

#12-4 AWG

NEMA configuration

6-50R

Torque rating

25 lbf-inch

Design type

Receptacle

Material

Glass filled nylon

Receptacle type

Two-pole, three-wire, grounding

Resources

Brochures

Flush mount receptacles sell sheet

Catalogs

Arrow Hart Buyers Guide Section B

Specifications and datasheets

Eaton Specification Sheet - 1254-BOX



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)