

# Conduit Bodies

Threaded and Set Screw Bodies and Kits



| Hub Size  | Unassembled (body only)<br>Catalog No. |           |             | Assembled (with cover and gasket)<br>Catalog No. |           |             | Box Quantity | Carton Quantity |
|-----------|--|-----------|-------------|--|-----------|-------------|--------------|-----------------|
|           | Threaded                               | Set Screw | Combination | Threaded   | Set Screw | Combination |              |                 |
| <b>LR</b> |  |           |             |  |           |             |              |                 |
| ½"        | 11821                                  | 1871      | 13821       | 12821  | 12871     | 14821       | 10           | 50              |
| ¾"        | 11822                                  | 11872     | 13822       | 12822  | 12872     | 14822       | 10           | 50              |
| 1"        | 11823                                  | 11873     | 13823       | 12823  | 12873     | 14823       | 5            | 25              |
| 1¼"       | 11824                                  | 11874     | 13824       | 12824  | 12874     | 14824       | —            | 2               |
| 1½"       | 11825                                  | 11875     | 13825       | 12825  | 12875     | 14825       | —            | 2               |
| 2"        | 11826                                  | 11876     | 13826       | 12826  | 12876     | 14826       | —            | 1               |
| 2½"       |  |           |             | 12827  |           |             | —            | 1               |
| 3"        |  |           |             | 12828  |           |             | —            | 1               |
| 3½"       |  |           |             | 12829  |           |             | —            | 1               |
| 4"        |  |           |             | 12830  |           |             | —            | 1               |
| <b>C</b>  |  |           |             |  |           |             |              |                 |
| ½"        | 11831                                  | 11881     | 13831       | 12831  | 12881     | 14831       | 10           | 50              |
| ¾"        | 11832                                  | 11882     | 13832       | 12832  | 12882     | 14832       | 10           | 50              |
| 1"        | 11833                                  | 11883     | 13833       | 12833  | 12883     | 14833       | 5            | 25              |
| 1¼"       | 11834                                  | 11884     | 13834       | 12834  | 12884     | 14834       | —            | 2               |
| 1½"       | 11835                                  | 11885     | 13835       | 12835  | 12885     | 14835       | —            | 2               |
| 2"        | 11836                                  | 11886     | 13836       | 12836  | 12886     | 14836       | —            | 1               |
| 2½"       |  |           |             | 12837  |           |             | —            | 1               |
| 3"        |  |           |             | 12838  |           |             | —            | 1               |
| <b>T</b>  |  |           |             |  |           |             |              |                 |
| ½"        | 11841                                  | 11891     | 13841       | 12841  | 12891     | 14841       | 10           | 50              |
| ¾"        | 11842                                  | 11892     | 13842       | 12842  | 12892     | 14842       | 10           | 50              |
| 1"        | 11843                                  | 11893     | 13843       | 12843  | 12893     | 14843       | 5            | 25              |
| 1¼"       | 11844                                  | 11894     | 13844       | 12844  | 12894     | 14844       | —            | 2               |
| 1½"       | 11845                                  | 11895     | 13845       | 12845  | 12895     | 14845       | —            | 2               |
| 2"        | 11846                                  | 11896     | 13846       | 12846  | 12896     | 14846       | —            | 1               |
| 2½"       |  |           |             | 12847  |           |             | —            | 1               |
| 3"        |  |           |             | 12848  |           |             | —            | 1               |

CONDUIT BODIES AND COVERS

# Conduit Bodies

Threaded and Set Screw Bodies and Kits



| Hub Size  | Unassembled (body only) |           |             | Assembled (with cover and gasket) |           |             | Box Quantity | Carton Quantity |
|-----------|-------------------------|-----------|-------------|-----------------------------------|-----------|-------------|--------------|-----------------|
|           | Threaded                | Set Screw | Combination | Threaded                          | Set Screw | Combination |              |                 |
| <b>LR</b> |                         |           |             |                                   |           |             |              |                 |
| 1/2"      | 11821                   | 1871      | 13821       | 12821                             | 12871     | 14821       | 10           | 50              |
| 3/4"      | 11822                   | 11872     | 13822       | 12822                             | 12872     | 14822       | 10           | 50              |
| 1"        | 11823                   | 11873     | 13823       | 12823                             | 12873     | 14823       | 5            | 25              |
| 1 1/4"    | 11824                   | 11874     | 13824       | 12824                             | 12874     | 14824       | —            | 2               |
| 1 1/2"    | 11825                   | 11875     | 13825       | 12825                             | 12875     | 14825       | —            | 2               |
| 2"        | 11826                   | 11876     | 13826       | 12826                             | 12876     | 14826       | —            | 1               |
| 2 1/2"    |                         |           |             | 12827                             |           |             | —            | 1               |
| 3"        |                         |           |             | 12828                             |           |             | —            | 1               |
| 3 1/2"    |                         |           |             | 12829                             |           |             | —            | 1               |
| 4"        |                         |           |             | 12830                             |           |             | —            | 1               |
| <b>C</b>  |                         |           |             |                                   |           |             |              |                 |
| 1/2"      | 11831                   | 11881     | 13831       | 12831                             | 12881     | 14831       | 10           | 50              |
| 3/4"      | 11832                   | 11882     | 13832       | 12832                             | 12882     | 14832       | 10           | 50              |
| 1"        | 11833                   | 11883     | 13833       | 12833                             | 12883     | 14833       | 5            | 25              |
| 1 1/4"    | 11834                   | 11884     | 13834       | 12834                             | 12884     | 14834       | —            | 2               |
| 1 1/2"    | 11835                   | 11885     | 13835       | 12835                             | 12885     | 14835       | —            | 2               |
| 2"        | 11836                   | 11886     | 13836       | 12836                             | 12886     | 14836       | —            | 1               |
| 2 1/2"    |                         |           |             | 12837                             |           |             | —            | 1               |
| 3"        |                         |           |             | 12838                             |           |             | —            | 1               |
| <b>T</b>  |                         |           |             |                                   |           |             |              |                 |
| 1/2"      | 11841                   | 11891     | 13841       | 12841                             | 12891     | 14841       | 10           | 50              |
| 3/4"      | 11842                   | 11892     | 13842       | 12842                             | 12892     | 14842       | 10           | 50              |
| 1"        | 11843                   | 11893     | 13843       | 12843                             | 12893     | 14843       | 5            | 25              |
| 1 1/4"    | 11844                   | 11894     | 13844       | 12844                             | 12894     | 14844       | —            | 2               |
| 1 1/2"    | 11845                   | 11895     | 13845       | 12845                             | 12895     | 14845       | —            | 2               |
| 2"        | 11846                   | 11896     | 13846       | 12846                             | 12896     | 14846       | —            | 1               |
| 2 1/2"    |                         |           |             | 12847                             |           |             | —            | 1               |
| 3"        |                         |           |             | 12848                             |           |             | —            | 1               |

CONDUIT BODIES AND COVERS