

Specifications

Eaton 1301-7B

Eaton toggle switch, #14-10 AWG, 15A, Flush, 120V, Side and push, Screw, Brown, Load type: Motor Control, Fan, LED, Incandescent, ELV, MLV, CFL, Fluorescent, Halogen, Single-Pole, Single-Pole, Polycarbonate

General specifications

PRODUCT NAME	Eaton toggle switch
CATALOG NUMBER	1301-7B
UPC	032664149108
PRODUCT LENGTH/DEPTH	1.31 in
PRODUCT HEIGHT	3.28 in
PRODUCT WIDTH	0.88 in
PRODUCT WEIGHT	0.102 lb
COMPLIANCES	RoHS Compliant NAFTA
CERTIFICATIONS	cULus Listed NOM
PRODUCT TYPE	Toggle switch



Powering Business Worldwide

Product specifications

TYPE Toggle switch

AMPERAGE RATING 15A

VOLTAGE RATING 120 V

NUMBER OF POLES Single-pole

APPLICATION Residential

WIRING METHOD Side and push

SWITCH TYPE Single-pole

MOUNTING METHOD Flush

CONNECTOR TYPE Screw

LOAD TYPE MLV
INC
ELV
FLR
Fan
HAL
CFL
Motor Control
LED

MATERIAL Polycarbonate

ALLOWABLE WIRE SIZE #14-10 AWG

TORQUE RATING 14 lbf-inch

COLOR Brown

Resources

SPECIFICATIONS AND DATASHEETS [Eaton Specification Sheet - 1301-7B](#)

[Residential grade toggle switches spec sheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

