

# Specifications

## Eaton 1303-7B

Eaton toggle switch, #14-10 AWG, 15A, Residential, Flush, 120V, Back and side, push wire, Screw, Brown, Load type: Motor Control, Fan, LED, Incandescent, ELV, MLV, CFL, Flourescent, Halogen, Single-Pole, Three-Way, Three-Way

### General specifications

<b>PRODUCT NAME</b>	Eaton toggle switch
<b>CATALOG NUMBER</b>	1303-7B
<b>UPC</b>	032664308802
<b>PRODUCT LENGTH/DEPTH</b>	1.31 in
<b>PRODUCT HEIGHT</b>	3.28 in
<b>PRODUCT WIDTH</b>	0.88 in
<b>PRODUCT WEIGHT</b>	0.14 lb
<b>COMPLIANCES</b>	RoHS Compliant NAFTA
<b>CERTIFICATIONS</b>	cULus Listed NOM
<b>PRODUCT TYPE</b>	Toggle switch



Powering Business Worldwide

## Product specifications

<b>TYPE</b>	Toggle switch
<b>AMPERAGE RATING</b>	15A
<b>VOLTAGE RATING</b>	120 V
<b>NUMBER OF POLES</b>	Single-pole
<b>APPLICATION</b>	Residential
<b>WIRING METHOD</b>	Back and side, push wire
<b>SWITCH TYPE</b>	Three-way
<b>MOUNTING METHOD</b>	Flush
<b>CONNECTOR TYPE</b>	Screw
<b>LOAD TYPE</b>	MLV Motor Control CFL ELV HAL FLR LED Fan INC
<b>MATERIAL</b>	Polycarbonate
<b>NUMBER OF WAYS</b>	Three-way
<b>ALLOWABLE WIRE SIZE</b>	#14-10 AWG
<b>TORQUE RATING</b>	14 lbf-inch
<b>COLOR</b>	Brown

## Resources

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - 1303-7B</a>
	<a href="#">Residential grade toggle switches spec sheet</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton 1303-7B

Eaton toggle switch, #14-10 AWG, 15A, Residential, Flush, 120V, Back and side, push wire, Screw, Brown, Load type: Motor Control, Fan, LED, Incandescent, ELV, MLV, CFL, Flourescent, Halogen, Single-Pole, Three-Way, Three-Way

### General specifications

<b>PRODUCT NAME</b>	Eaton toggle switch
<b>CATALOG NUMBER</b>	1303-7B
<b>UPC</b>	032664308802
<b>PRODUCT LENGTH/DEPTH</b>	1.31 in
<b>PRODUCT HEIGHT</b>	3.28 in
<b>PRODUCT WIDTH</b>	0.88 in
<b>PRODUCT WEIGHT</b>	0.14 lb
<b>COMPLIANCES</b>	RoHS Compliant NAFTA
<b>CERTIFICATIONS</b>	cULus Listed NOM
<b>PRODUCT TYPE</b>	Toggle switch



Powering Business Worldwide

## Product specifications

<b>TYPE</b>	Toggle switch
<b>AMPERAGE RATING</b>	15A
<b>VOLTAGE RATING</b>	120 V
<b>NUMBER OF POLES</b>	Single-pole
<b>APPLICATION</b>	Residential
<b>WIRING METHOD</b>	Back and side, push wire
<b>SWITCH TYPE</b>	Three-way
<b>MOUNTING METHOD</b>	Flush
<b>CONNECTOR TYPE</b>	Screw
<b>LOAD TYPE</b>	MLV Motor Control CFL ELV HAL FLR LED Fan INC
<b>MATERIAL</b>	Polycarbonate
<b>NUMBER OF WAYS</b>	Three-way
<b>ALLOWABLE WIRE SIZE</b>	#14-10 AWG
<b>TORQUE RATING</b>	14 lbf-inch
<b>COLOR</b>	Brown

## Resources

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - 1303-7B</a>
	<a href="#">Residential grade toggle switches spec sheet</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

