

Specifications

Eaton 1303-7B

Eaton toggle switch, #14-10 AWG, 15A, Residential, Flush, 120V, Back and side, push wire, Screw, Brown, Load type: Motor Control, Fan, LED, Incandescent, ELV, MLV, CFL, Flourescent, Halogen, Single-Pole, Three-Way, Three-Way

General specifications

PRODUCT NAME	Eaton toggle switch
CATALOG NUMBER	1303-7B
UPC	032664308802
PRODUCT LENGTH/DEPTH	1.31 in
PRODUCT HEIGHT	3.28 in
PRODUCT WIDTH	0.88 in
PRODUCT WEIGHT	0.14 lb
COMPLIANCES	RoHS Compliant NAFTA
CERTIFICATIONS	cULus Listed NOM
PRODUCT TYPE	Toggle switch



Powering Business Worldwide

Product specifications

TYPE	Toggle switch
AMPERAGE RATING	15A
VOLTAGE RATING	120 V
NUMBER OF POLES	Single-pole
APPLICATION	Residential
WIRING METHOD	Back and side, push wire
SWITCH TYPE	Three-way
MOUNTING METHOD	Flush
CONNECTOR TYPE	Screw
LOAD TYPE	MLV Motor Control CFL ELV HAL FLR LED Fan INC
MATERIAL	Polycarbonate
NUMBER OF WAYS	Three-way
ALLOWABLE WIRE SIZE	#14-10 AWG
TORQUE RATING	14 lbf-inch
COLOR	Brown

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - 1303-7B
	Residential grade toggle switches spec sheet

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

