



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 14102AQD03 Comet Ac/DC Visible Reflex With Micro Connector

Eaton Corp

Catalog Number	14102AQD03
Manufacturer	Eaton Corp
Description	Eaton Comet 18MM Tubular Photoelectric Sensor, Retroreflective, Forward Viewing, Output On, Dual Key Micro, 300 Ma Ac/DC At 20-264 Vac/15-30 VDC, 4 Pin, Ac: L1 Switched, DC: NPN Open Collector, 20-264 Vac 50/60 HZ, 15-30 VDC (NPN)
Weight per unit	0.7000 (lbs/each)
Product Category	Photoelectric Sensors

### Features

connection	Dual key micro
dimensions	2.2000 IN X 0.4700 IN X 0.7100 IN

### Dimensions and Weight

Height	0.71
Length	2.2
Width	0.47

### Descriptions

Description	COMET AC/DC VISIBLE REFLEX WITH MICRO CONNECTOR
extra long description	ETN 14102AQD03 18MM ACDC VISIBLE RE
Features	Eaton's Comet Series Photoelectric Sensors is a complete line of high performance, 18 mm tubular sensors with a variety of models and modes to solve virtually any sensing problem.
Long Description	Eaton Comet 18mm tubular photoelectric sensor, Retroreflective, Forward Viewing, Output ON, Dual key micro, 300 mA AC/DC at 20-264 Vac/15-30 Vdc, 4 pin, AC: L1 switched, DC: NPN open collector, 20-264 Vac 50/60 Hz, 15-30 Vdc (NPN)
Product Type	18MM Acdc Visible Reflex W/Micro Conn

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113843681
Manufacturers Part Number	14102AQD03
UPC	782113843681

### Taxonomies, Classifications, and Categories

Category Description	PROXIMITY SWITCHES AND CORDSETS
Type	Tubular photoelectric sensor

### Packaging

Carton	1
Weight Per each	0.7



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application .....	Vehicles: On-Road - PickUp & Delivery: Food .....
Operating Temperature .....	-40° to 158°F (-40° to 70°C) .....
standard .....	UL Recognized,cUL Recognized .....