

E-Z BORE® SELF-FEED WOOD BORING BITS



UP TO
4X
FASTER*

- **FAST** - MORE HOLES. LESS TIME. NO SLUG REMOVAL.*
- **SMOOTH** - CLEAN HOLES. LESS SPLINTERS. NO BLOWOUTS.
- **LONG-LASTING** - HARDENED CARBON ALLOY. DUAL CUTTING EDGES. REPLACEABLE TIP.

*Compared to bi-metal hole saws

USA PHONE 800.435.0786 FAX 800.451.2632
CANADA PHONE 866.384.8813 FAX 800.524.2853
INT'L PHONE +1.815.397.7070 FAX +1.815.397.9247




GREENLEE®
A Textron Company

E-Z BORE®

SELF-FEED WOOD BORING BITS

FOR PRODUCT VIDEOS, DEMONSTRATIONS
AND MORE, SCAN THIS QR CODE OR VISIT:
www.youtube.com/GreenleeDEMO



149H2KIT
Contractor Kit, 7pc



FEATURES

- Self-feed tip pulls bit through wood.
- Outer spur teeth reduce splintering and blowouts.
- Available from 1" to 4-5/8" sizes - perfect for installing 1/2" to 4" conduit and pipe.

ORDERING INFORMATION

E-Z BORE® SELF-FEED BITS

CAT. NO.	UPC NO.	PIPE & CONDUIT SIZE	HOLE DIA.		LENGTH	
			INCH	MM	INCH	MM
149H2-1	01247	1/2"	1"	25.4	5"	127.0
149H2-1-1/8	01250	1/2"	1-1/8"	28.6	5"	127.0
149H2-1-1/4	01249	3/4"	1-1/4"	31.8	5"	127.0
149H2-1-3/8	01252	3/4"	1-3/8"	34.9	5"	127.0
149H2-1-1/2	01248	1"	1-1/2"	38.1	5"	127.0
149H2-1-3/4	01251	1-1/4"	1-3/4"	44.4	5"	127.0
149H2-2	01257	1-1/4"	2"	50.8	5"	127.0
149H2-2-1/8	01260	1-1/2"	2-1/8"	54	5"	127.0
149H2-2-1/4	01258	1-1/2"	2-1/4"	57.2	5"	127.0
149H2-2-9/16	01261	2"	2-9/16"	65.1	5"	127.0
149H2-3	01262	2-1/2"	3"	76.2	5"	127.0
149H2-3-5/8	01263	3"	3-5/8"	92.1	6-1/4"	158.8
149H2-4-5/8	01272	4"	4-5/8"	117.5	6-1/4"	158.8

E-Z BORE® CONTRACTOR KIT

- Seven of the most common E-Z BORE® bits from 1" to 2-9/16"
- Also includes 5-1/2" bit extension, replacement screw points, hex wrench, and set screws.

CAT. NO.	UPC NO.	DESCRIPTION	PIPE & CONDUIT SIZE	HOLE DIA.	
				INCH	MM
149H2KIT	01273	Contractor Kit, 7pc	1/2" to 2"	1" to 2-9/16"	25.4 to 65.1
34997	34997	Plastic Case			

E-Z BORE® BIT EXTENSION

CAT. NO.	UPC NO.	DESCRIPTION	HEX SHANK SIZE		LENGTH	
			INCH	MM	INCH	MM
904H2-5-1/2	01266	Bit Extension	7/16"	11.1	5-1/2"	140.0

E-Z BORE® SCREW POINTS

CAT. NO.	UPC NO.	DESCRIPTION	SCREW POINT DIA.		LENGTH	
			INCH	MM	INCH	MM
149H2-1/4	01254	Screw Point	1/4"	6.4	2"	50.8
149H2-3/8	01271	Screw Point	3/8"	9.5	2-3/4"	69.9

Distributed by



www.greenlee.com • MA-5917 03/13
4455 Boeing Drive • Rockford, IL 61109-2988 • USA • 815-397-7070
©2013 Greenlee Textron Inc. • An ISO 9001 Company • Printed in USA
Greenlee Textron Inc. is a subsidiary of Textron Inc.

E-Z BORE® SELF-FEED WOOD BORING BITS



UP TO
4X
FASTER*

- **FAST** - MORE HOLES. LESS TIME. NO SLUG REMOVAL.*
- **SMOOTH** - CLEAN HOLES. LESS SPLINTERS. NO BLOWOUTS.
- **LONG-LASTING** - HARDENED CARBON ALLOY. DUAL CUTTING EDGES. REPLACEABLE TIP.


*Compared to bi-metal hole saws



E-Z BORE®

SELF-FEED WOOD BORING BITS

FOR PRODUCT VIDEOS, DEMONSTRATIONS AND MORE, SCAN THIS QR CODE OR VISIT:
www.youtube.com/GreenleeDEMO



149H2KIT
Contractor Kit, 7pc



FEATURES

- Self-feed tip pulls bit through wood.
- Outer spur teeth reduce splintering and blowouts.
- Available from 1" to 4-5/8" sizes - perfect for installing 1/2" to 4" conduit and pipe.

ORDERING INFORMATION

E-Z BORE® SELF-FEED BITS

CAT. NO.	UPC NO.	PIPE & CONDUIT SIZE	HOLE DIA.		LENGTH	
			INCH	MM	INCH	MM
149H2-1	01247	1/2"	1"	25.4	5"	127.0
149H2-1-1/8	01250	1/2"	1-1/8"	28.6	5"	127.0
149H2-1-1/4	01249	3/4"	1-1/4"	31.8	5"	127.0
149H2-1-3/8	01252	3/4"	1-3/8"	34.9	5"	127.0
149H2-1-1/2	01248	1"	1-1/2"	38.1	5"	127.0
149H2-1-3/4	01251	1-1/4"	1-3/4"	44.4	5"	127.0
149H2-2	01257	1-1/4"	2"	50.8	5"	127.0
149H2-2-1/8	01260	1-1/2"	2-1/8"	54	5"	127.0
149H2-2-1/4	01258	1-1/2"	2-1/4"	57.2	5"	127.0
149H2-2-9/16	01261	2"	2-9/16"	65.1	5"	127.0
149H2-3	01262	2-1/2"	3"	76.2	5"	127.0
149H2-3-5/8	01263	3"	3-5/8"	92.1	6-1/4"	158.8
149H2-4-5/8	01272	4"	4-5/8"	117.5	6-1/4"	158.8

E-Z BORE® CONTRACTOR KIT

- Seven of the most common E-Z BORE® bits from 1" to 2-9/16"
- Also includes 5-1/2" bit extension, replacement screw points, hex wrench, and set screws.

CAT. NO.	UPC NO.	DESCRIPTION	PIPE & CONDUIT SIZE	HOLE DIA.	
				INCH	MM
149H2KIT	01273	Contractor Kit, 7pc	1/2" to 2"	1" to 2-9/16"	25.4 to 65.1
34997	34997	Plastic Case			

E-Z BORE® BIT EXTENSION

CAT. NO.	UPC NO.	DESCRIPTION	HEX SHANK SIZE		LENGTH	
			INCH	MM	INCH	MM
904H2-5-1/2	01266	Bit Extension	7/16"	11.1	5-1/2"	140.0

E-Z BORE® SCREW POINTS

CAT. NO.	UPC NO.	DESCRIPTION	SCREW POINT DIA.		LENGTH	
			INCH	MM	INCH	MM
149H2-1/4	01254	Screw Point	1/4"	6.4	2"	50.8
149H2-3/8	01271	Screw Point	3/8"	9.5	2-3/4"	69.9

Distributed by



www.greenlee.com • MA-5917 03/13
 4455 Boeing Drive • Rockford, IL 61109-2988 • USA • 815-397-7070
 ©2013 Greenlee Textron Inc. • An ISO 9001 Company • Printed in USA
 Greenlee Textron Inc. is a subsidiary of Textron Inc.