



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 15502 2 Blade Pocket Knife, Steel, 2-1/2" Blade *Klein Tools*

Catalog Number	15502
Manufacturer	Klein Tools
Description	Klein'S Portable Pocket Knife Includes Standard Spearpoint and Screwdriver Tip Blades. The Sturdy Blades Are Made Of Carbon Steel. For Convenience, The Screwdriver Tip Blade Can Lock In The Open Position.
Weight per unit	0.2500 (lbs/each)
Product Category	Miscellaneous Hand Tools

### Features

Blade Length	2.5" (6.4 cm)
blade type	Standard Spearpoint, Screwdriver-Tip
Material	Carbon Steel

### Material, Color, and Finish

Blade Material	CARBON STEEL
Handle Color	Blue
Handle Material	Plastic with Faux Wood Grain

### Dimensions and Weight

Overall Length	6.625" (16.8 cm)
----------------	------------------

### Descriptions

Description	2 BLADE POCKET KNIFE, STEEL, 2-1/2" BLADE
extra long description	KLEIN 1550-2 2 Blade Pocket Knife S
Features	Klein's portable pocket knife includes standard spearpoint and screwdriver tip blades. The sturdy blades are made of carbon steel. For convenience, the screwdriver tip blade can lock in the open position.
Long Description	Klein's portable pocket knife includes standard spearpoint and screwdriver tip blades. The sturdy blades are made of carbon steel. For convenience, the screwdriver tip blade can lock in the open position.
Product Type	2 Blade Pocket Knife Steel 2-1/2"

### Manufacturer Information

Brand	Klein Tools
GTIN	00092644442025
Manufacturers Part Number	1550-2
UPC	092644442025



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	BITS, BLADES, AND HOLE SAWS
Type	Pocket Knife

## Packaging

Carton	1
Package	6
Weight	4.0 oz (113 g)
Weight Per each	0.25