



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2351 Walnut Hill Lane Suite 150
75229-0000, TX Dallas
Phone: 214-351-0785
Fax: 972-241-1564



1597GRY Radiant Self Test Duplex Gfci 15A 125V Gy

Pass & Seymour/Legrand

Catalog Number	1597GRY
Manufacturer	Pass & Seymour/Legrand
Description	Duplex Receptacle, 15 A, 125 V, 2 Poles, #14 to #10 Awg Compatible Wire Size, Control Circuit Actuator, Back and Side Wired Connection, 60 HZ, 1.73 In Width, 4.20 In Height, Thermoplastic Material, Gray, 0.025 Sec Trip Time
Weight per unit	0.2750 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

actuator	Control Circuit
amperage rating	15
connection	Back and side wire
indoor/outdoor	Indoor
interrupt rating	4 to 6 mA
Mounting Type	Box
Number of Gangs	1.0
Outlet Type	Self-Test, GFCI
Poles	2
trip range	4 to 6 mA
Trip Type	.025 Second Nominal
Voltage Rating	125

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Length	1.03
Width	1.73

Descriptions

Description	RADIANT SELF TEST DUPLEX GFCI 15A 125V GY
extra long description	P&S 1597GRY RADIANT SLF TST DUP GFC

Manufacturer Information

Brand	Pass & Seymour
GTIN	00785007035841
UPC	785007035841

Taxonomies, Classifications, and Categories

Category Description	Residential GFCI devices
Type	Outlet



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2351 Walnut Hill Lane Suite 150
75229-0000, TX Dallas
Phone: 214-351-0785
Fax: 972-241-1564

Trade Size

Amperage.....15.0

Packaging

Carton.....1

Package.....10

Weight Per each.....0.275

Uses, Certifications, and Standards

environmental conditions.....95% Humidity, UL 94 V2

Operating Temperature.....-35°C to +66°C

standard.....CULUS, UL, cULus, UL Listed, FSUL