



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 200AWPK6 \*Delisted\* 200W 120V A21 Med Base Frost Incan Lamp

*Ge By Current Lamps*

|                  |   |
|------------------|---|
| Catalog Number   | 200AWPK6  |
| Manufacturer     | Ge By Current Lamps   |
| Description      | A-Line Incandescent Lamp, 2800 K, 3405 LM Brightness (Lumens), 200 W, 120.1 V, Soft White, CC-8 Filament, 750 H Average Life, Medium Screw-In Base, Non Dimmable, 2.625 In Diameter, 5.37 In Length, 0.2 LB |
| Weight per unit  | 0.2000 (lbs/each)   |
| Product Category | Line A, P, PS Shape Lamps   |

### Features

|         |                    |
|---------|--------------------|
| Base    | Medium Screw (E26) |
| lumens  | 3405               |
| Wattage | 200                |

### Material, Color, and Finish

|       |       |
|-------|-------|
| Color | White |
|-------|-------|

### Descriptions

|             |  |
|-------------|--|
| Description | *DELISTED* 200W 120V A21 MED BASE FROST INCAN LAMP |
|-------------|--|

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | GE Current     |
| GTIN                      | 00043168445344 |
| Manufacturers Part Number | 200A/W-PK6     |
| UPC                       | 043168445344   |

### Taxonomies, Classifications, and Categories

|                      |              |
|----------------------|--------------|
| Category Description | INCANDESCENT |
|----------------------|--------------|

### Availability

|                     |          |
|---------------------|----------|
| Manufacturer Status | Inactive |
|---------------------|----------|

### Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Package         | 6   |
| Weight Per each | 0.2 |

### Uses, Certifications, and Standards

|             |          |
|-------------|----------|
| Application | STANDARD |
|-------------|----------|