



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2097HGI Self Test Gfci Hosp GRD Recp 20A 12 Iv

Pass & Seymour/LeGrand

Catalog Number	2097HGI
Manufacturer	Pass & Seymour/LeGrand
Description	Self-Test Duplex Receptacle, 20 A, 125 V, 2 Poles, #14 to #10 Awg Compatible Wire Size, Control Circuit Actuator, Back and Side Wired Connection, 60 HZ, 1.73 In Width, 4.20 In Height, Thermoplastic Material, Ivory, 0.025 Sec Trip Time, Impact Resistant, 0.2800 LB
Weight per unit	0.2750 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

actuator	Control Circuit
amperage rating	20
connection	Back and side wire
interrupt rating	4 to 6 mA
media	Yes
Poles	2
trip range	4 to 6 mA
Trip Type	.025 Second Nominal
Voltage Rating	125

Dimensions and Weight

Length	1.03
Width	1.73

Descriptions

Description	SELF TEST GFCI HOSP GRD RECP 20A 12 IV
extra long description	P&S 2097HGI SELF-TEST GFCI HOS GRD

Manufacturer Information

Brand	Pass & Seymour
GTIN	00785007035933
UPC	785007035933

Taxonomies, Classifications, and Categories

Category Description	Residential GFCI devices
Type	Hospital Grade 20A Self Test Duplex GFCI

Packaging

Carton	1
Package	10
Weight Per each	0.275



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

environmental conditions	95% Humidity, UL 94 V2
Operating Temperature	-35°C to +66°C
standard	cULus, UL Listed, FSUL