



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2097TRW Radiant Self Test TR Gfci 20A 125V WH

Pass & Seymour/LeGrand

Catalog Number	2097TRW
Manufacturer	Pass & Seymour/LeGrand
Description	Self-Test Duplex Receptacle, 20 A, 125 V, 2 Poles, #14 to #10 Awg Compatible Wire Size, Control Circuit Actuator, Back and Side Wired Connection, 60 HZ, 1.73 In Width, 4.20 In Height, Thermoplastic Material, White, 0.025 Sec Trip Time, Tamper Resistant, 0.2800 LB
Weight per unit	0.2750 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

actuator	Control Circuit
amperage rating	20
connection	Back and side wire
indoor/outdoor	Indoor
interrupt rating	4 to 6 mA
Mounting Type	Box
Number of Gangs	1.0
Outlet Type	Self-Test, Indoor, GFCI, Tamper-Resistant, Residential
Poles	Double Pole
trip range	4 to 6 mA
Trip Type	.025 Second Nominal
Voltage	125.0 V
Voltage Rating	125

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Length	1.03
Width	1.73

Descriptions

Description	RADIANT SELF TEST TR GFCI 20A 125V WH
extra long description	P&S 2097TRW RADIANT SELF TEST TR GF

Manufacturer Information

Brand	Pass & Seymour
GTIN	00785007035872
UPC	785007035872

Taxonomies, Classifications, and Categories

Category Description	Residential GFCI devices
Type	Outlet



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Trade Size

Amperage 20.0

Packaging

Carton 1

Package 10

Weight Per each 0.275

Uses, Certifications, and Standards

environmental conditions 95% Humidity, UL 94 V2

Operating Temperature -35°C to +66°C

standard UL, cULus