

UPGRADE. OUTWORK. OUTLAST.


UP TO **3X** MORE RUN-TIME
UP TO **20%** MORE POWER
OVER **2X** MORE LIFE



REDLITHIUM CP3.0/XC6.0

M12 REDLITHIUM BATTERIES GUIDE

LIGHT DEMAND ← **FITS M12 TOOLS** → HEAVY DEMAND



CP Less weight and smaller size

48-11-2430
M12™ REDLITHIUM™ CP3.0 Battery Pack

48-11-2420
M12™ REDLITHIUM™ CP2.0 Battery Pack

48-11-2401
M12™ REDLITHIUM™ CP1.5 Battery Pack



XC More power and run-time

48-11-2460
M12™ REDLITHIUM™ XC6.0 Battery Pack

48-11-2440
M12™ REDLITHIUM™ XC4.0 Battery Pack

48-11-2402
M12™ REDLITHIUM™ XC3.0 Battery Pack

48-11-2411 2-Pack
48-11-2412 2-Pack




USB Rechargeable 700L Focusing Flashlight Kit

2110-21

Lumens	700 / 100 / 700
Modes	High, Low, Strobe
Beam Focus	Slide, Spot/Flood
Water & Dust Rating	IP67
Height	6.5"
Powered By	REDLITHIUM™ USB



Includes: (1) REDLITHIUM™ USB Battery Pack, 2 ft Heavy Duty USB Cord





USB Rechargeable Hard Hat Headlamp Kit

2111-21

Lumens	475 / 300 / 300 / 150 / 25
Modes	Spot/Flood, Spot – High, Flood – High/Medium/Low
Water & Dust Rating	IP54
Powered By	REDLITHIUM™ USB



Includes: (1) REDLITHIUM™ USB Battery Pack, 2 ft Heavy Duty USB Cord, Hard Hat Clips





USB Rechargeable ROVER™ Magnetic Flood Light Kit

2112-21

Lumens	445 / 100
Modes	High, Low
Hands-Free	Dual Magnets
Water & Dust Rating	IP54
Height	6.0"
Powered By	REDLITHIUM™ USB



Includes: (1) REDLITHIUM™ USB Battery Pack, 2 ft Heavy Duty USB Cord





USB Rechargeable Pivoting Flashlight Kit

2113-21

Lumens	500 / 400 / 100
Modes	Spot – High, Flood – High, Flood – Low
Pivoting Head	110°
Water & Dust Rating	IP54
Height	6.3"
Powered By	REDLITHIUM™ USB



Includes: (1) REDLITHIUM™ USB Battery Pack, 2 ft Heavy Duty USB Cord



USB Rechargeable ROVER™ Pivoting Flood Light Kit

2114-21

Lumens	550 / 250 / 100
Modes	High, Medium, Low
Pivoting Head	210°
Water & Dust Rating	IP54
Height	4.4"
Powered By	REDLITHIUM™ USB



Includes: (1) REDLITHIUM™ USB Battery Pack, 2 ft Heavy Duty USB Cord

REDLITHIUM™ USB Battery Pack

48-11-2130

Specifications:

Amp Hours	2.4
Cell Chemistry	LITHIUM-ION
Voltage	4V



REDLITHIUM™ USB Charger

48-59-2002

Specifications:

Cell Chemistry	LITHIUM-ION
On-Board Indicator Light	Yes
Cell Voltage Monitoring	Yes



Includes: REDLITHIUM™ USB Charger, 2 ft Heavy Duty USB Cord

REDLITHIUM™ USB Battery & Charger

48-59-2003

Includes: (1) REDLITHIUM™ USB Battery Pack, REDLITHIUM™ USB Charger, AC Wall Block



MILWAUKEE® Penlight

2105

Lumens	100
Water & Dust Rating	IP67
Height	5.4"
Powered By	(2) AAA



MILWAUKEE® Headlamp

2106

Lumens	300 / 150 / 25
Modes	High, Medium, Low
Water & Dust Rating	IP54
Powered By	(3) AAA



325L Focusing Flashlight

2107

Lumens	325 / 25
Modes	High, Low
Beam Focus	Slide, Spot/Flood
Water & Dust Rating	IP67
Height	5.0"
Powered By	(3) AAA



2107S: Also Includes Holster

Magnetic Flood Light

2108

Lumens	300 / 100
Modes	High, Low
Water & Dust Rating	IP54
Height	4.8"
Powered By	(2) AA



UPGRADE. OUTWORK. OUTLAST.

UP TO **3X** MORE RUN-TIME
UP TO **20%** MORE POWER
OVER **2X** MORE LIFE

REDLITHIUM CP3.0/XC6.0

M12 REDLITHIUM BATTERIES GUIDE

LIGHT DEMAND ← **FITS M12 TOOLS** → HEAVY DEMAND

CP Less weight and smaller size

48-11-2430 M12™ REDLITHIUM™ CP3.0 Battery Pack

48-11-2420 M12™ REDLITHIUM™ CP2.0 Battery Pack

48-11-2401 M12™ REDLITHIUM™ CP1.5 Battery Pack



XC More power and run-time

48-11-2460 M12™ REDLITHIUM™ XC6.0 Battery Pack

48-11-2440 M12™ REDLITHIUM™ XC4.0 Battery Pack

48-11-2402 M12™ REDLITHIUM™ XC3.0 Battery Pack

48-11-2411 2-Pack
48-11-2412 2-Pack



USB Rechargeable 700L Focusing Flashlight Kit

2110-21

Lumens	700 / 100 / 700
Modes	High, Low, Strobe
Beam Focus	Slide, Spot/Flood
Water & Dust Rating	IP67
Height	6.5"
Powered By	REDLITHIUM™ USB

Includes: (1) REDLITHIUM™ USB Battery Pack, 2 ft Heavy Duty USB Cord



REDLITHIUM™ USB Battery Pack

48-11-2130

Specifications:

Amp Hours	2.4
Cell Chemistry	LITHIUM-ION
Voltage	4V



USB Rechargeable Hard Hat Headlamp Kit

2111-21

Lumens	475 / 300 / 300 / 150 / 25
Modes	Spot/Flood, Spot – High, Flood – High/Medium/Low
Water & Dust Rating	IP54
Powered By	REDLITHIUM™ USB

Includes: (1) REDLITHIUM™ USB Battery Pack, 2 ft Heavy Duty USB Cord, Hard Hat Clips



REDLITHIUM™ USB Charger

48-59-2002

Specifications:

Cell Chemistry	LITHIUM-ION
On-Board Indicator Light	Yes
Cell Voltage Monitoring	Yes

Includes: REDLITHIUM™ USB Charger, 2 ft Heavy Duty USB Cord



USB Rechargeable ROVER™ Magnetic Flood Light Kit

2112-21

Lumens	445 / 100
Modes	High, Low
Hands-Free	Dual Magnets
Water & Dust Rating	IP54
Height	6.0"
Powered By	REDLITHIUM™ USB

Includes: (1) REDLITHIUM™ USB Battery Pack, 2 ft Heavy Duty USB Cord



MILWAUKEE® Penlight

2105

Lumens	100
Water & Dust Rating	IP67
Height	5.4"
Powered By	(2) AAA



USB Rechargeable Pivoting Flashlight Kit

2113-21

Lumens	500 / 400 / 100
Modes	Spot – High, Flood – High, Flood – Low
Pivoting Head	110°
Water & Dust Rating	IP54
Height	6.3"
Powered By	REDLITHIUM™ USB



Includes: (1) REDLITHIUM™ USB Battery Pack, 2 ft Heavy Duty USB Cord



MILWAUKEE® Headlamp

2106

Lumens	300 / 150 / 25
Modes	High, Medium, Low
Water & Dust Rating	IP54
Powered By	(3) AAA



USB Rechargeable ROVER™ Pivoting Flood Light Kit

2114-21

Lumens	550 / 250 / 100
Modes	High, Medium, Low
Pivoting Head	210°
Water & Dust Rating	IP54
Height	4.4"
Powered By	REDLITHIUM™ USB

Includes: (1) REDLITHIUM™ USB Battery Pack, 2 ft Heavy Duty USB Cord



325L Focusing Flashlight

2107

Lumens	325 / 25
Modes	High, Low
Beam Focus	Slide, Spot/Flood
Water & Dust Rating	IP67
Height	5.0"
Powered By	(3) AAA



2107S: Also Includes Holster

Magnetic Flood Light

2108

Lumens	300 / 100
Modes	High, Low
Water & Dust Rating	IP54
Height	4.8"
Powered By	(2) AA

