



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2107 120/277V 2000W SPST Conduit Mount Die Cast Zinc

Nsi Industries

Catalog Number	2107
Manufacturer	Nsi Industries
Description	Conduit Mount, 208 to 277 V, 2000 W, 2 In Width, 3-3/4 In Height, Die Cast Zinc Housing Material, SPST Switch Type, Cadmium Coated CDS Photocell Sensor, -40 °F Operating Temperature, +140 °F Operating Temperature, Conduit Mount, 0.6 LB/Ea
Weight per unit	0.6000 (lbs/each)
Product Category	Lighting Photocells

Features

supply voltage	120-277 VAC
Timing Range	2 Minutes

Dimensions and Weight

Size	.500 Conduit Mount
------	--------------------

Descriptions

Description	120/277V 2000W SPST CONDUIT MOUNT DIE CAST ZINC
-------------	---

Manufacturer Information

GTIN	00786261600318
UPC	786261600318

Taxonomies, Classifications, and Categories

Type	Die Cast Zinc Photocontrol
------	----------------------------

Availability

Manufacturer Status	Inactive
Status	Inactive

Packaging

Carton	1
Weight Per each	0.6

Uses, Certifications, and Standards

Application	Parking Lot-Building Perimeter-Outdoor Signage Lighting
Enclosure	Zinc Diecast
environmental conditions	-40 to + 140 F
Frequency Rating	50-60 Hz
Mounting	Conduit Mount
Operating Temperature	-40 to + 140 F
standard	UL-CSA