



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

PRODUCT  
IMAGE  
COMING  
SOON

## 2107A 120/277V 2000W SPST Conduit Mo

*Nsi Industries*

Catalog Number	2107A
Manufacturer	Nsi Industries
Description	Spec Grade 1/2" Stem Diecast Zinc, On 1-5FC/Off 3-15FC, 6"Leads, 120/208-277 Vac, 2000W Tungsten, 1800VA Ballast, 600VA Led
Weight per unit	0.6000 (lbs/each)
Product Category	Lighting Controls

### Features

supply voltage	120 /208-277 VAC
Timing Range	0-2 min

### Dimensions and Weight

Size	.500 Conduit Mount IN
------	-----------------------

### Descriptions

Description	120/277V 2000W SPST CONDUIT MO
extra long description	TORK 2107A Photocontrol Stem Alumin
Long Description	Spec Grade 1/2" Stem DieCast Zinc, On 1-5fc/Off 3-15fc, 6"Leads, 120/208-277 VAC, 2000W Tungsten, 1800VA Ballast, 600VA LED
Product Type	Photocontrol Stem Aluminum 208-277V
Special Features	1/2 Conduit Mount - Time Delay On And Off - Cadmium Sulphide Epoxy Coated 1 Diameter Cell IN

### Manufacturer Information

Brand	98010027731
GTIN	00786261620347
Manufacturers Part Number	2107A
sub brand	Photocontrols
UPC	786261620347

### Taxonomies, Classifications, and Categories

Category Description	Commercial dimmers, motion sensors, & photo cells
Type	Die Cast Zinc Photocontrol

### Availability

Status	Inactive
--------	----------

### Packaging

Carton	1
Weight Per each	0.6



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Parking Lot-Building Perimeter-Outdoor Signage Lighting
Enclosure	Zinc Diecast
environmental conditions	-40 to 140 F
Frequency Rating	50-60 Hz
Mounting	Conduit Mount
Operating Temperature	-40 to + 140 F
standard	UL-CSA