



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



222413 LN Splicing Connector, 3COND, 28-12 Awg, Gy *Wago Corporation*

Catalog Number	222413
Manufacturer	Wago Corporation
Description	Splicing Connector, Aluminum;Copper Conductor Material, Non-Insulated, Gray Insulation Color, Made In Usa, 12 Awg;2.5 MM^2 Maximum Conductor Size, +85 °C Maximum Operating Temperature, 400 V Maximum Voltage Rating, 0.08 MM^2;28 Awg Minimum Conductor Size, +40 °C Minimum Operating Temperature, 0.571 In;14.5 MM Overall Length, UI International Germany GMBH;UI Underwriters Laboratories Inc Standards Met, 2-Conductor Terminal Terminal Type, 4.283 G Weight
Weight per unit	0.4721 (lbs/each)
Product Category	Splicing & Terminating Kits

Descriptions

Description	LN SPLICING CONNECTOR, 3COND, 28-12 AWG, GY
-------------	---

Manufacturer Information

Manufacturers Part Number	222-413/K194-4045
---------------------------	-------------------

Taxonomies, Classifications, and Categories

Category Description	Residential cord connectors
----------------------	-----------------------------

Packaging

Carton	1
Weight Per each	0.4721