



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

ALL-DAY RUN-TIME



234B21S M12 Women'S Heated Axis Jacket - Black - S *Milwaukee Electric Tool*

| | |
|------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number | 234B21S |
| Manufacturer | Milwaukee Electric Tool |
| Description | The Milwaukee® M12™ Women'S Heated Axis™ Jacket Delivers Heat Built For Lightweight Durability. Powered By Milwaukee® M12™ Redlithium™ Battery Technology, This Lightweight and Durable Jacket Features An Advanced Heat Technology System Utilizing Carbon Fiber Heating Elements and Quick-Heat Functionality, Distributing Heat 3X Faster Than Market Competitors to The Chest, Back and Shoulders. A Hidden Battery Pass-Thru Pocket Construction Allows For Front or Back Battery Placement, Increasing Comfort and Versat |
| Weight per unit | 3.5 (lbs/each) |
| Product Category | Tools & Testers |

Features

| | |
|--------------------|------|
| batteries included | YES |
| battery life | 12 |
| Voltage | 12.0 |
| Water Resistant | Yes |

Material, Color, and Finish

| | |
|---------------------|-----------|
| Insulation Material | Polyester |
| Jacket Color | BLACK |

Descriptions

| | |
|------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description | M12 WOMEN'S HEATED AXIS JACKET - BLACK - S |
| extra long description | MILW 234B-21S Women's Heated Jacket |
| Features | The M12 series offers solutions that deliver portable productivity. They take on the tightest spaces and are specifically built to go anywhere. They are trade focused, system wide, lightweight with ergonomic design make portability easy, and operation faster and more productive. |
| Long Description | The MILWAUKEE® M12™ Women's Heated AXIS™ Jacket delivers HEAT BUILT FOR LIGHTWEIGHT DURABILITY. Powered by MILWAUKEE® M12™ REDLITHIUM™ Battery Technology, this lightweight and durable jacket features an advanced heat technology system utilizing carbon fiber heating elements and Quick-Heat functionality, distributing heat 3X faster than market competitors to the chest, back and shoulders. A hidden battery pass-thru pocket construction allows for front or back battery placement, increasing comfort and versat |
| Product Type | Women'S Heated Jacket Kit Black S |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Milwaukee® |
| GTIN | 00045242658435 |
| Manufacturers Part Number | 234B-21S |
| UPC | 045242658435 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------------|
| Category Description | Job Site & Safety Apparel |
|----------------------|---------------------------|

Availability

| | |
|--------|----------|
| Status | Inactive |
|--------|----------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 3.54 |