



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 242020 M12 Hackzall Reciprocating Saw - Tool Only

*Milwaukee Electric Tool*

Catalog Number	242020
Manufacturer	Milwaukee Electric Tool
Description	At Only 11 In. and 2.6 LBS, The Hackzall® M12™ Cordless Lithium-Ion Reciprocating Saw Features A Compact and Light Weight Design For Superior Control and Versatility In Tight Spaces. A Powerful Motor Delivers 0-3, 000 Strokes Per Minute and A 1/2 In. Stroke Length Allows For Fast Cutting Through A Wide Range Of Material Such As Drywall, Wood, and PVC. The Variable Speed Trigger Allows For A Controlled Cut While A Quik-Lok™ Blade Clamp Offers Fast and Easy Blade Changes.
Weight per unit	2.6 (lbs/each)
Product Category	Battery Driven Tools

### Features

Battery Voltage	12
charge time	0.5
media	Yes
Stroke Length	0.5
Switch Type	Trigger

### Material, Color, and Finish

Housing Material	Metal
------------------	-------

### Dimensions and Weight

Height	2
Length	11
Width	4



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	M12 HACKZALL RECIPROCATING SAW - TOOL ONLY
extra long description	MILW 2420-20 12V Hackzall Saw TO
Features	The M12 series offers solutions that deliver portable productivity. They take on the tightest spaces and are specifically built to go anywhere. They are trade focused, system wide, lightweight with ergonomic design make portability easy, and operation faster and more productive.
Long Description	At only 11 in. and 2.6 lbs, the HACKZALL® M12™ cordless lithium-ion reciprocating saw features a compact and light weight design for superior control and versatility in tight spaces. A powerful motor delivers 0-3,000 strokes per minute and a 1/2 in. stroke length allows for fast cutting through a wide range of material such as drywall, wood, and PVC. The variable speed trigger allows for a controlled cut while a QUIK-LOK™ blade clamp offers fast and easy blade changes.
Product Type	12V Hackzall Saw to
Special Features	Only 11 IN And 2.6 LB For Cutting In Tight Spaces; Keyless QUIK-LOK Blade Clamp Allows For Quick And Easy Blade Changes; All-Metal Gear Case For Added Durability; Variable Speed Trigger For Increased User Control; Battery Fuel Gauge Displays Remaining Run-Time; Accepts Both HACKZALL And SAWZALL Style Blades (See Related Products For Listing Of HACKZALL Blades); Built-In LED Light Illuminates Work Surface; SfpM: 0 - 3000 SPM; Tool Weight: 2.200 LB; Blade Clamp: QUIK-LOK Universal 1/2 IN Tang; Trigger: Varia

## Manufacturer Information

Brand	Milwaukee®
GTIN	00045242158638
Manufacturers Part Number	2420-20
UPC	045242158638

## Taxonomies, Classifications, and Categories

Category Description	POWER TOOLS
Type	CORDLESS

## Packaging

Carton	1
Package	10
Weight Per each	2.64

## Uses, Certifications, and Standards

Application	For Fast Cutting Through A Wide Range Of Material Such As Drywall, Wood, And PVC
-------------	--