



255SRTI 2" Ins Steel Emt Raintight Compression Conn

Nsi Industries

Catalog Number	255SRTI
Manufacturer	Nsi Industries
Description	Compression Connector, 2 In Trade Size, Straight Connection Orientation, Zinc Electro-Plated, Insulated, 3-7/32 In Length, 2-5/8 In Diameter, +105 °C Operating Temperature, 0.068 LB/Ea
Weight per unit	0.0680 (lbs/each)
Product Category	Steel Insulated Straight Compr

Features

Connector Type	Steel Raintight/Concrete-Tight Insulated
insulation	Insulated Throat
media	Yes

Material, Color, and Finish

Finish	Zinc Electroplated
--------	--------------------

Dimensions and Weight

Size	2
------	---

Descriptions

Description	2" INS STEEL EMT RAINIGHT COMPRESSION CONN
extra long description	BPT 255-SRTI 2 IN Steel Raintight C

Manufacturer Information

Brand	Bridgeport
GTIN	00781747122551
UPC	781747122551

Taxonomies, Classifications, and Categories

Category Description	STEEL EMT FITTINGS
Type	CONNECTOR

Trade Size

Trade Size	2
------------	---

Packaging

Carton	10
Weight Per each	0.068

Uses, Certifications, and Standards

Application	Used to join EMT to box or enclosure. Concrete tight/Raintight. Insulated Throat - 105°C. Patented
standard	cULus