



# M18™ Cordless LITHIUM-ION 2-Tool Combo Kit



2691-22



## What's Included

- (1) M18™ Compact 1/2" Drill Driver (Bare Tool) (2606-20)
- (1) M18™ 1/4" Hex Impact Driver (Bare Tool) (2656-20)
- (2) M18™ Compact REDLITHIUM™ Battery (48-11-1815)
- (1) M18™ & M12™ Multi-Voltage Charger (48-59-1812)
- (1) Contractor Bag

## Where to Buy

-  Shop Online
-  Find Local

## Overview

The 2691-22 M18™ Cordless 2-Tool Combo Kit includes the M18™ Compact Driver (2606-20) and the M18™ 1/4" Hex Impact Driver (2656-20). The M18™ Cordless LITHIUM-ION System's patented technologies and electronics, innovative motor design, and superior ergonomics provide the most efficient blend of power, weight and performance in the industry. Powered by RED LITHIUM™, the M18 cordless LITHIUM-ION system delivers more torque, more power, and longer run-time than the competition.



## Features

- Milwaukee® 4-Pole Frameless Motor: Features a robust design combined with rare-earth magnets for longer life, best-in-class 500 in-lbs of torque and 0-400/0-1,800 RPM
- Compact Design: Allows greater accessibility in tight work spaces.
- All-Metal Gear Case and Chuck: Provide maximum impact and shock durability
- REDLINK™ Intelligence: Advanced overload protects the tool against abusive situations and provides maximum life

## Specifications

<b>Voltage</b>	18V
<b>Length</b>	7-1/4"
<b>Weight</b>	2.9 lbs
<b>LED Light</b>	Yes
<b>Peak Torque</b>	500 in-lbs
<b>Chuck Type</b>	1/2" Metal Single Sleeve - Ratcheting Lock
<b>Speed</b>	0-400/ 0-1,800 RPM

<b>Tool Warranty</b>	5 Years
----------------------	---------



**M18™ 1/4" Hex Impact Driver (Bare Tool)**  
 Cat. # 2656-20

**Features**

- Milwaukee® 4-Pole Frameless Motor: Features a robust design for longer life, more power and more runtime than any brushed competitor
- Milwaukee® designed Impact Mechanism: Delivers maximum power and application speed for greater efficiency on the job
- REDLINK™ Intelligence: Provides optimized performance and overload protection using total system communication between tool, battery and charger
- 1/4" Hex Quick-Connect Chuck

**Specifications**

<b>Voltage</b>	18V
<b>Length</b>	5-1/2"
<b>Weight</b>	3.1 lbs
<b>No Load RPM</b>	0-2,750
<b>On Board FUEL Gauge</b>	Fuel Gauge on Battery
<b>LED Light</b>	Yes
<b>Anvil Size and Type</b>	1/4" Hex Quick Change
<b>No Load IPM</b>	0-3,450
<b>Torque</b>	1,500 in-lbs
<b>Package Type</b>	Tool-Only (No Battery or Charger Included)
<b>Tool Warranty</b>	5 Years



# M18™ Cordless LITHIUM-ION 2-Tool Combo Kit



2691-22



## What's Included

- (1) M18™ Compact 1/2" Drill Driver (Bare Tool) (2606-20)
- (1) M18™ 1/4" Hex Impact Driver (Bare Tool) (2656-20)
- (2) M18™ Compact REDLITHIUM™ Battery (48-11-1815)
- (1) M18™ & M12™ Multi-Voltage Charger (48-59-1812)
- (1) Contractor Bag

## Where to Buy

-  Shop Online
-  Find Local

## Overview

The 2691-22 M18™ Cordless 2-Tool Combo Kit includes the M18™ Compact Driver (2606-20) and the M18™ 1/4" Hex Impact Driver (2656-20). The M18™ Cordless LITHIUM-ION System's patented technologies and electronics, innovative motor design, and superior ergonomics provide the most efficient blend of power, weight and performance in the industry. Powered by RED LITHIUM™, the M18 cordless LITHIUM-ION system delivers more torque, more power, and longer run-time than the competition.



## Features

- Milwaukee® 4-Pole Frameless Motor: Features a robust design combined with rare-earth magnets for longer life, best-in-class 500 in-lbs of torque and 0-400/0-1,800 RPM
- Compact Design: Allows greater accessibility in tight work spaces.
- All-Metal Gear Case and Chuck: Provide maximum impact and shock durability
- REDLINK™ Intelligence: Advanced overload protects the tool against abusive situations and provides maximum life

## Specifications

<b>Voltage</b>	18V
<b>Length</b>	7-1/4"
<b>Weight</b>	2.9 lbs
<b>LED Light</b>	Yes
<b>Peak Torque</b>	500 in-lbs
<b>Chuck Type</b>	1/2" Metal Single Sleeve - Ratcheting Lock
<b>Speed</b>	0-400/ 0-1,800 RPM

<b>Tool Warranty</b>	5 Years
----------------------	---------



**M18™ 1/4" Hex Impact Driver (Bare Tool)**  
 Cat. # 2656-20

**Features**

- Milwaukee® 4-Pole Frameless Motor: Features a robust design for longer life, more power and more runtime than any brushed competitor
- Milwaukee® designed Impact Mechanism: Delivers maximum power and application speed for greater efficiency on the job
- REDLINK™ Intelligence: Provides optimized performance and overload protection using total system communication between tool, battery and charger
- 1/4" Hex Quick-Connect Chuck

**Specifications**

<b>Voltage</b>	18V
<b>Length</b>	5-1/2"
<b>Weight</b>	3.1 lbs
<b>No Load RPM</b>	0-2,750
<b>On Board FUEL Gauge</b>	Fuel Gauge on Battery
<b>LED Light</b>	Yes
<b>Anvil Size and Type</b>	1/4" Hex Quick Change
<b>No Load IPM</b>	0-3,450
<b>Torque</b>	1,500 in-lbs
<b>Package Type</b>	Tool-Only (No Battery or Charger Included)
<b>Tool Warranty</b>	5 Years