


# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5018 W Main Street 74701-0000, OK Durant Phone: 580-745-5448





### 29W75 Turnlok Conn IP67 30A 3PH 250V L1530R Pass & Seymour/Legrand

Catalog Number	29W75
Manufacturer	Pass & Seymour/Legrand
Description	Locking Watertight Connector, 30AMP 3 250VOLT, Nema
	Configuration L15-30, Multipoint Sealing System Provides
	Environmental Protection Of Nema 4, 4X, 6, 6P, and IP67 Rated.
Weight per unit	0.8300 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out
atures	

#### **Feat**

tures	
amperage rating	30
Cord Type	12/4 S to 8/4 S, 6/4 MSHA, .640" min to .930" max
indoor/outdoor	Both
Material	Rubber
Number of Phases	3.0
Number of Wires	4.0
Phase	Three
Poles	3-way
Voltage	125.0 V
Voltage Rating	250
Wire Size	12 - 6 AWG

## Material, Color, and Finish

Color	Yellow	

# **Descriptions**

Description	TURNLOK CONN IP67 30A 3PH 250V L1530R
extra long description	P&S 29W75 TLCONN IP67 30A 3PH 250V
Features	Watertight
Long Description	Locking Watertight Connector, 30amp 3 250volt, NEMA
	Configuration L15-30, multipoint sealing system provides
	environmental protection of NEMA 4, 4X, 6, 6P, and IP67 rated.
Product Type	Tlconn IP67 30A 3PH 250V L1530R
Special Features	Rated watertight for 1,500 psi high-pressure hosedown, P&S
	Turnlok® watertight plugs & connectors feature rugged
	construction, multiple seals to ensure protection against the
	environment and ease of installation.



# ELLIOTT ELECTRIC SUPPLY 5018 W Main Street 74701-0000, OK Durant Phone: 580-745-5448

We Deliver...Lower Cost, Quality Products, & Personal Service

Fax: 580-745-5449

Manufacturer Inform	ation	
---------------------	-------	--

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007033496
Manufacturers Part Number	29W75
UPC	785007033496

### **Taxonomies, Classifications, and Categories**

Category Description	Residential receptacles	
Туре	CONNECTOR	

### **Trade Size**

\mnorago	30.0
Amperage	30.0

### **Packaging**

, kayiriy		
Carton	1	
Package	10	
Weight Per each	0.83	

### Uses, Certifications, and Standards

es, cei illications, and standards	
Application	High-pressure washdowns. Particle build-up. Condensation. Corrosive substances. Food and beverage processing plants can be harsh, challenging environments. Fortunately, we have a full menu of electrical devices that keep things running smoothly while protecting people and equipment. IEC PIN & SLEEVE DEVICES Watertight Plugs & Connectors   Thermoplastic elastomer body resists water, oils, lubricants and soaps while maintaining NEMA 4, 4X, 6, 6P, and IP65, 66, 67 ratings   Ideal for washdown areas — rated wa
environmental conditions	Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed materials are UV stabilized
nema rating	L15-30R
standard	UL Listed, CSA Listed