

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301470108](#)  
**Status:** **Active**  
**Overview:** [Watertite Wet-Location Wiring Solutions](#)  
**Description:** Watertite Connector with Locking Blade, 3 Pole/4 Wire, NEMA L16-30, 3ø 480V, Cord Grip Body Size F4

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA                      LR6837  
 UL                        E10176

**General**

Product Family                      Wiring Devices  
 Series                                  [130147](#)  
 Exclude SD Check                      Yes  
 IP Rating                                IP67  
 NEMA Configuration                      NEMA L16-30  
 Overview                                [Watertite Wet-Location Wiring Solutions](#)  
 Product Literature Order No              987650-8067  
 Product Name                              Watertite  
 Receptacle Type                          Single  
 Specialty                                 N/A  
 Type                                        Connector  
 UPC                                         78678871334

**Physical**

Cord Grip Body Size                      F4 1"  
 Flange                                      No  
 Flip Lid                                      No  
 Gender                                        Female  
 Length                                        N/A  
 Locking Blade                                Yes  
 Net Weight                                 441.798/g  
 Poles                                         3-pole/4-wire

**Electrical**

Cord Type                                    N/A  
 Current - Maximum per Contact              30.0A  
 GFCI                                         No  
 Lighted Connector                          No  
 Voltage - Maximum                          3ø 480V

**Material Info**

Engineering Number                          29W76



**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130147 Series](#)

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301470108](#)  
**Status:** **Active**  
**Overview:** [Watertite Wet-Location Wiring Solutions](#)  
**Description:** Watertite Connector with Locking Blade, 3 Pole/4 Wire, NEMA L16-30, 3ø 480V, Cord Grip Body Size F4

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA                      LR6837  
 UL                        E10176

**General**

Product Family                      Wiring Devices  
 Series                                  [130147](#)  
 Exclude SD Check                      Yes  
 IP Rating                                IP67  
 NEMA Configuration                      NEMA L16-30  
 Overview                                [Watertite Wet-Location Wiring Solutions](#)  
 Product Literature Order No              987650-8067  
 Product Name                              Watertite  
 Receptacle Type                          Single  
 Specialty                                N/A  
 Type                                        Connector  
 UPC                                        78678871334

**Physical**

Cord Grip Body Size                      F4 1"  
 Flange                                    No  
 Flip Lid                                    No  
 Gender                                    Female  
 Length                                    N/A  
 Locking Blade                              Yes  
 Net Weight                                441.798/g  
 Poles                                        3-pole/4-wire

**Electrical**

Cord Type                                  N/A  
 Current - Maximum per Contact              30.0A  
 GFCI                                        No  
 Lighted Connector                          No  
 Voltage - Maximum                          3ø 480V

**Material Info**

Engineering Number                          29W76



**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130147 Series](#)