












| CATALOG NUMBER | DESCRIPTION | UPC CODE | WEIGHT | CASE QTY | PALLET QTY | NJ | IL | TX | CA | GA |
|----------------|-------------|----------|--------|----------|------------|----|----|----|----|----|
|----------------|-------------|----------|--------|----------|------------|----|----|----|----|----|

Paralux III High Performance


EP3GAX Series

| | | | | | | | | | | | | |
|--|-------------------------------|---|--------------|------|---|----|---|---|---|---|---|---|
|  | 2'x2' - 9 Cell | | | | | | | | | | | |
| | AP32U | 2 U-LAMP, 2'X2' STATIC PARABOLIC, 9 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8 W/LAMPS & FLEX | 080083520176 | 16.1 | 1 | 32 | | | | ★ |  | |
| | 2EP3GAVX-2U6T8S33I-UNV-EB81-U | 2 U-LAMP, 2'X2' AIR SUPPLY PARABOLIC, W/VANES, 9 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8 | 080083520220 | 14.3 | 1 | 40 | • | • | | | ★ |  |
| | 2EP3GX-2U6T8S33I-UNV-EB81-U | 2 U-LAMP, 2'X2' STATIC PARABOLIC, 9 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8 | 080083520145 | 14.3 | 1 | 36 | • | • | • | • | • | ★ |
| | 2EP3GX-317S33I-UNV-EB81-U | 3 LAMP, 2'X2' STATIC PARABOLIC, 9 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8 | 080083520084 | 14.3 | 1 | 40 | | • | | | ★ | |

| | | | | | | | | | | | |
|--|---------------------------|---|--------------|-------|---|----|--|--|--|--|---|
|  | 2'x4' - 12 Cell | | | | | | | | | | |
| | 2EP3GX-232S26I-UNV-EB81-U | 2 LAMP, 2'X4' STATIC PARABOLIC, 12 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8 | 080083520169 | 27.36 | 1 | 20 | | | | | ★ |

| | | | | | | | | | | | | | |
|--|--|--|--------------|-------|---|----|---|---|---|---|---|---|---|
|  | 2'x4' - 18 Cell | | | | | | | | | | | | |
| | AP3 | 3 LAMP, 2'X4' AIR SUPPLY PARABOLIC W/VANES, 18 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8 W/LAMPS & FLEX | 622696199785 | 27.36 | 1 | 16 | | | | | ★ |  | |
| | 2EP3GAVX-332S36I-UNV-EB81-U | 3 LAMP, 2'X4' AIR SUPPLY PARABOLIC, W/VANES, 18 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8 | 662401000685 | 27.36 | 1 | 20 | • | • | | | | ★ |  |
| | 2EP3GAX-332S36I-UNV-EB81-U | 3 LAMP, 2'X4' AIR SUPPLY PARABOLIC, 18 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8 | 662401339785 | 27.36 | 1 | 20 | | | | | | ★ | |
| | 2EP3GX-232S36I-UNV-EB81-U | 2 LAMP, 2'X4' STATIC PARABOLIC, 18 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8 | 080083520237 | 27.36 | 1 | 20 | | | | | | ★ | |
| | 2EP3GX-332S36I-UNV-EB81-U | 3 LAMP, 2'X4' STATIC PARABOLIC, 18 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8 | 662401012084 | 27.36 | 1 | 20 | • | • | • | • | • | ★ |  |
| | 2EP3GX-332S36I-UNV-EB82-U | 3 LAMP, 2'X4' STATIC PARABOLIC, 18 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, TWO - CEE LISTED ELECTRONIC BALLAST, T8 | 662401339761 | 27.36 | 1 | 20 | | • | • | • | • | ★ | |
| | 2EP3GX-332S36I-UNV-L8735-A3/8-2/18G-EB81-U | 3 LAMP, 2'X4' STATIC PARABOLIC, 18 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8, W/LAMPS & FLEX | 662401339730 | 27.36 | 1 | 20 | | • | | | | ★ |  |
| | 2EP3GX-332S36I-UNV-L8735-EB81-U | 3 LAMP, 2'X4' STATIC PARABOLIC, 18 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8 W/LAMPS | 662400201908 | 27.36 | 1 | 20 | • | • | • | | | ★ |  |
| | 2EP3GX-332S36I-UNV-L8741-EB81-U | 3 LAMP, 2'X4' STATIC PARABOLIC, 18 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8 W/LAMPS | 622697478087 | 27.36 | 1 | 20 | | | | | | ★ |  |

| | | | | | | | | | | | | |
|--|---------------------------|---|--------------|-------|---|----|--|--|--|--|---|--|
| | 2'x4' - 32 Cell | | | | | | | | | | | |
| | 2EP3GX-432S48I-UNV-EB81-U | 4 LAMP, 2'X4' STATIC PARABOLIC, 32 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8 W/LAMPS | 080083520206 | 27.36 | 1 | 20 | | | | | ★ | |

| | | | | | | | | | | | |
|--|--|---|--------------|-------|---|----|--|---|--|--|---|
|  | Chicago Approved - 2'x2' 9 Cell | | | | | | | | | | |
| | ATW-SW4-2EP3GAVX-2U6T8S33I-UNV-EB81-U | 2 U-LAMP, 2'X2' AIR SUPPLY PARABOLIC W/VANES, 9 CELL SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, ELECTRONIC BALLAST, T8, CHICAGO PLENUM APPROVED | 623961053474 | 16.47 | 1 | 32 | | • | | | ★ |

Parabolic Surface High Performance

Standard 3" Parabolic


| | | | | | | | | | | | | |
|------------------|---|--------------|-----|---|----|--|--|--|--|--|---|--|
| EP3X-S36I-24-C-U | REPLACEMENT LOUVER, 2EP3, 18 CELL, SEMI-SPECULAR, 2'X4' | 080083684380 | 6.2 | 1 | 20 | | | | | | ★ | |
|------------------|---|--------------|-----|---|----|--|--|--|--|--|---|--|


★ Indicates ARRA Eligible Product **E** Indicates EISA Compliant Pulse Start Products  Indicates Off the Shelf Product


| CATALOG NUMBER | DESCRIPTION | UPC CODE | WEIGHT | CASE PALLET | | | | | |
|----------------|-------------|----------|--------|-------------|-----|----|----|----|----|
| | | | | QTY | QTY | NJ | IL | TX | CA |

Paralux III High Performance


EP3GAX Series

| | | | | | | | | | | | |
|--|-------------------------------|---|--------------|------|---|----|--|--|--|--|-----|
|  | 2'x2' - 9 Cell | | | | | | | | | | |
| | AP32U | 2 U-LAMP, 2'X2' STATIC PARABOLIC, 9 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8 W/LAMPS & FLEX | 080083520176 | 16.1 | 1 | 32 | | | | | ★ Ⓢ |
| | 2EP3GAVX-2U6T8S33I-UNV-EB81-U | 2 U-LAMP, 2'X2' AIR SUPPLY PARABOLIC, W/VANES, 9 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8 | 080083520220 | 14.3 | 1 | 40 | | | | | ★ Ⓢ |
| | 2EP3GX-2U6T8S33I-UNV-EB81-U | 2 U-LAMP, 2'X2' STATIC PARABOLIC, 9 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8 | 080083520145 | 14.3 | 1 | 36 | | | | | ★ Ⓢ |
| | 2EP3GX-317S33I-UNV-EB81-U | 3 LAMP, 2'X2' STATIC PARABOLIC, 9 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8 | 080083520084 | 14.3 | 1 | 40 | | | | | ★ |

| | | | | | | | | | | | |
|--|---------------------------|---|--------------|-------|---|----|--|--|--|--|---|
|  | 2'x4' - 12 Cell | | | | | | | | | | |
| | 2EP3GX-232S26I-UNV-EB81-U | 2 LAMP, 2'X4' STATIC PARABOLIC, 12 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8 | 080083520169 | 27.36 | 1 | 20 | | | | | ★ |

| | | | | | | | | | | | |
|--|--|--|--------------|-------|---|----|--|--|--|--|-----|
|  | 2'x4' - 18 Cell | | | | | | | | | | |
| | AP3 | 3 LAMP, 2'X4' AIR SUPPLY PARABOLIC W/VANES, 18 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8 W/LAMPS & FLEX | 622696199785 | 27.36 | 1 | 16 | | | | | ★ Ⓢ |
| | 2EP3GAVX-332S36I-UNV-EB81-U | 3 LAMP, 2'X4' AIR SUPPLY PARABOLIC, W/VANES, 18 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8 | 662401000685 | 27.36 | 1 | 20 | | | | | ★ Ⓢ |
| | 2EP3GAX-332S36I-UNV-EB81-U | 3 LAMP, 2'X4' AIR SUPPLY PARABOLIC, 18 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8 | 662401339785 | 27.36 | 1 | 20 | | | | | ★ |
| | 2EP3GX-232S36I-UNV-EB81-U | 2 LAMP, 2'X4' STATIC PARABOLIC, 18 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8 | 080083520237 | 27.36 | 1 | 20 | | | | | ★ |
| | 2EP3GX-332S36I-UNV-EB81-U | 3 LAMP, 2'X4' STATIC PARABOLIC, 18 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8 | 662401012084 | 27.36 | 1 | 20 | | | | | ★ Ⓢ |
| | 2EP3GX-332S36I-UNV-EB82-U | 3 LAMP, 2'X4' STATIC PARABOLIC, 18 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, TWO - CEE LISTED ELECTRONIC BALLAST, T8 | 662401339761 | 27.36 | 1 | 20 | | | | | ★ |
| | 2EP3GX-332S36I-UNV-L8735-A3/8-2/18G-EB81-U | 3 LAMP, 2'X4' STATIC PARABOLIC, 18 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8, W/LAMPS & FLEX | 662401339730 | 27.36 | 1 | 20 | | | | | ★ Ⓢ |
| | 2EP3GX-332S36I-UNV-L8735-EB81-U | 3 LAMP, 2'X4' STATIC PARABOLIC, 18 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8 W/LAMPS | 662400201908 | 27.36 | 1 | 20 | | | | | ★ Ⓢ |
| | 2EP3GX-332S36I-UNV-L8741-EB81-U | 3 LAMP, 2'X4' STATIC PARABOLIC, 18 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8 W/LAMPS | 622697478087 | 27.36 | 1 | 20 | | | | | ★ Ⓢ |

| | | | | | | | | | | | |
|--|---------------------------|---|--------------|-------|---|----|--|--|--|--|---|
| | 2'x4' - 32 Cell | | | | | | | | | | |
| | 2EP3GX-432S48I-UNV-EB81-U | 4 LAMP, 2'X4' STATIC PARABOLIC, 32 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8 W/LAMPS | 080083520206 | 27.36 | 1 | 20 | | | | | ★ |

| | | | | | | | | | | | |
|--|--|---|--------------|-------|---|----|--|--|--|--|---|
|  | Chicago Approved - 2'x2' 9 Cell | | | | | | | | | | |
| | ATW-SW4-2EP3GAVX-2U6T8S33I-UNV-EB81-U | 2 U-LAMP, 2'X2' AIR SUPPLY PARABOLIC W/VANES, 9 CELL SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, ELECTRONIC BALLAST, T8, CHICAGO PLENUM APPROVED | 623961053474 | 16.47 | 1 | 32 | | | | | ★ |

Parabolic Surface High Performance

Standard 3" Parabolic

| | | | | | | | | | | | |
|------------------|---|--------------|-----|---|----|--|--|--|--|--|---|
| EP3X-S36I-24-C-U | REPLACEMENT LOUVER, 2EP3, 18 CELL, SEMI-SPECULAR, 2'X4' | 080083684380 | 6.2 | 1 | 20 | | | | | | ★ |
|------------------|---|--------------|-----|---|----|--|--|--|--|--|---|

★ Indicates ARRA Eligible Product Ⓢ Indicates EISA Compliant Pulse Start Products Ⓢ Indicates Off the Shelf Product