



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2RC10 12-10 Nylon Ins Butt Splice

Abb Installation Products, Inc

Catalog Number	2RC10
Manufacturer	Abb Installation Products, Inc
Description	Nylon-Insulated Butt Splice, Length 1.26 Inches, Width .28 Inches, Maximum Insulation Diameter .210, Wire Range #12-#10 Awg, Color Yellow, Copper, Tin Plated
Weight per unit	0.0080 (lbs/each)
Product Category	Small Terminals & Connectors

Features

Material	Copper
Voltage Rating	600 V

Material, Color, and Finish

Color	Yellow
Finish	Electro -Tin Plated

Descriptions

Description	12-10 NYLON INS BUTT SPLICE
extra long description	ABB 2RC10 INS NYLON BUTT SPLICE 12-
Long Description	Nylon-Insulated Butt Splice, Length 1.26 Inches, Width .28 Inches, Maximum Insulation Diameter .210, Wire Range #12-#10 AWG, Color Yellow, Copper, Tin Plated
Product Type	Ins Nylon Butt Splice 12-10 Awg
Special Features	Nylon insulated splices meet or exceed the requirements of MIL-T-7928. These splices are color-coded according to wire size

Manufacturer Information

Brand	Sta-Kon
GTIN	00786210800226
Manufacturers Part Number	2RC10
UPC	786210800226

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Nylon Insulated Butt Splice

Availability

minimum qty	50
-------------	----

Packaging

Carton	50
Package	250
Weight Per each	0.008



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

standard	UL E9809 / UL E9809
Temperature Rating	105 C