



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 300MIF130VPK3 \*Delisted\* 300W 130V PS25 Frost Med Base Incand *Ge By Current Lamps*

Catalog Number	300MIF130VPK3
Manufacturer	Ge By Current Lamps
Description	A-Line Incandescent Lamp, 2950 K, 6120 LM Brightness (Lumens), 300 W, 130 V, Inside Frost, CC-8 Filament, 750 H Average Life, Medium Base, Non Dimmable, 3.125 In Diameter, 6.93 In Length, 0.22 LB
Weight per unit	0.2200 (lbs/each)
Product Category	Line A, P, PS Shape Lamps

### Features

Base	Medium Screw (E26)
lumens	6120
Voltage Rating	130
Wattage	300

### Material, Color, and Finish

Color	INSIDE FROST
-------	--------------

### Descriptions

Description	*DELISTED* 300W 130V PS25 FROST MED BASE INCAND
-------------	---

### Manufacturer Information

Brand	GE Current
GTIN	00043168737906
Manufacturers Part Number	300M/IF/130V-PK3
UPC	043168737906

### Taxonomies, Classifications, and Categories

Category Description	INCANDESCENT
----------------------	--------------

### Availability

Manufacturer Status	Inactive
---------------------	----------

### Packaging

Carton	1
Package	3
Weight Per each	0.22

### Uses, Certifications, and Standards

Application	STANDARD
-------------	----------