



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 301033 In-Sure Push-In Wire Conn, 33 3-Port Org, 100/Box

*Ideal*

|                  |   |
|------------------|---|
| Catalog Number   | 301033  |
| Manufacturer     | Ideal   |
| Description      | Ideal, Wire Connector, In-Sure, Push-In, Size: 0.780 In Length X 0.690 In Width X 0.380 In Height, Connection: 3 Ports, Wire Size: #12 Awg - #20 Awg Solid, #12 Awg - #16 Awg (19 Strand or Less) #18 Awg (7 Strand) Stranded, #14 Awg - #18 Awg (19 Strand or Less) Stranded (Tin Bonded), Color: Orange, Voltage Rating: 600 V Maximum Building Wire, 1000 V Maximum Signs and Lighting Fixtures, Temperature Rating: 105 Deg C Shell Rated, Wire Type: Solid, Stranded, Stranded (Tin Bonded), Model: 33 |
| Weight per unit  | 0.0050 (lbs/each)   |
| Product Category | Electrical Fixture Conn ( Nuts  |

### Features

|                |   |
|----------------|---|
| connection     | 3 Ports   |
| Voltage Rating | 600 V Maximum Building Wire, 1000 V Maximum Signs And Lighting Fixtures   |
| Wire Size      | #12 AWG - #20 AWG Solid, #12 AWG - #16 AWG (19 Strand Or Less) #18 AWG (7 Strand) Stranded, #14 AWG - #18 AWG (19 Strand Or Less) Stranded (Tin Bonded) |
| Wire Type      | Solid, Stranded, Stranded (Tin Bonded)  |

### Material, Color, and Finish

|       |        |
|-------|--------|
| Color | Orange |
|-------|--------|

### Dimensions and Weight

|      |  |
|------|--|
| Size | 0.780 IN Length X 0.690 IN Width X 0.380 IN Height |
|------|--|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |   |
|------------------------|---|
| Description            | IN-SURE PUSH-IN WIRE CONN, 33 3-PORT ORG, 100/BOX   |
| extra long description | IDEAL 30-1033 PUSH-IN 12AWG 3-PORT,   |
| Features               | Ergonomic design for easy grip and comfortable installationLow insertion force for fast and easy connectionsCompact size makes installation easyClear shell gives visual verification of connectionTough, UL 94V-2 flame-retardant shell rated at 105°C (221°F)Approved for bonding and grounding applicationsStrip, push, connect – the fastest way to make a connection.The In-Sure Push-In Wire Connector is perfect for residential, light commercial, lighting retrofit, and pre-fab wiring systems, or any other branch c |
| Long Description       | IDEAL, Wire Connector, In-Sure, Push-In, Size: 0.780 IN Length X 0.690 IN Width X 0.380 IN Height, Connection: 3 Ports, Wire Size: #12 AWG - #20 AWG Solid, #12 AWG - #16 AWG (19 Strand Or Less) #18 AWG (7 Strand) Stranded, #14 AWG - #18 AWG (19 Strand Or Less) Stranded (Tin Bonded), Color: Orange, Voltage Rating: 600 V Maximum Building Wire, 1000 V Maximum Signs And Lighting Fixtures, Temperature Rating: 105 DEG C Shell Rated, Wire Type: Solid, Stranded, Stranded (Tin Bonded), Model: 33                     |
| Product Type           | Push-In 12AWG 3-Port, 100 Box   |
| Special Features       | Features: No-Twist Connection Reduces Repetitive Motion Fatigue; Low Insertion Force For Fast And Easy Connections; Compact Size Makes Installation Easy; Clear Shell Gives Visual Verification Of Connection; UL Listed To 486C And CSA Certified To C22.2 #188; UL 467 Listed For Grounding And Bonding Applications; 600V Maximum Building Wire, 1000V; Maximum Signs And Lighting Fixtures; Shell Rated To 105 DEG C; Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 DEG F); Model: 33                       |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Ideal          |
| GTIN                      | 00783250693542 |
| Manufacturers Part Number | 30-1033        |
| UPC                       | 783250693542   |

## Taxonomies, Classifications, and Categories

|                      |           |
|----------------------|-----------|
| Category Description | WIRE NUTS |
| Type                 | Push-In   |

## Availability

|             |     |
|-------------|-----|
| minimum qty | 100 |
|-------------|-----|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

|                 |       |
|-----------------|-------|
| Carton          | 100   |
| Package         | 1000  |
| Weight Per each | 0.005 |

## Uses, Certifications, and Standards

|                    |  |
|--------------------|--|
| Application        | For Grounding And Bonding Applications   |
| standard           | CSA C22.2 #188, 486C/467 UL Listed, RoHS |
| Temperature Rating | 105 DEG C Shell Rated                    |