



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



301034J In-Sure Push-In Wire Conn, 34 4-Port Yel, 200/Jar

Ideal

Catalog Number	301034J
Manufacturer	Ideal
Description	Push-In Wire Connector, Yellow Insulation Color, +221 °F Operating Temperature, 0.780 In Overall Length, 0.820 In Overall Width, 0.380 In Overall Height, 600 V (Building Wire);1000 V (Maximum Signs/Lighting Fixture), 0.01 LB
Weight per unit	0.0080 (lbs/each)
Product Category	Electrical Fixture Conn (Nuts

Features

connection	4 Ports
Voltage Rating	600 V Maximum Building Wire, 1000 V Maximum Signs And Lighting Fixtures
Wire Size	#12 AWG - #20 AWG Solid, #12 AWG - #16 AWG (19 Strand Or Less) #18 AWG (7 Strand) Stranded, #14 AWG - #18 AWG (19 Strand Or Less) Stranded (Tin Bonded)
Wire Type	Solid, Stranded, Stranded (Tin Bonded)

Material, Color, and Finish

Color	Yellow
-------	--------

Dimensions and Weight

Size	0.780 IN Length X 0.820 IN Width X 0.380 IN Height
------	----------------------------------------------------

Descriptions

Description	IN-SURE PUSH-IN WIRE CONN, 34 4-PORT YEL, 200/JAR
extra long description	IDEAL 30-1034J PUSH-IN 12AWG 4-PORT
Features	Ergonomic design for easy grip and comfortable installationLow insertion force for fast and easy connectionsCompact size makes installation easyClear shell gives visual verification of connectionTough, UL 94V-2 flame-retardant shell rated at 105°C (221°F)Approved for bonding and grounding applicationsStrip, push, connect – the fastest way to make a connection.The In-Sure Push-In Wire Connector is perfect for residential, light commercial, lighting retrofit, and pre-fab wiring systems, or any other branch c

Manufacturer Information

Brand	Ideal
GTIN	00783250693580
UPC	783250693580



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
Type	Push-In

Availability

minimum qty	200
-------------	-----

Packaging

Carton	200
Package	1200
Weight Per each	0.008

Uses, Certifications, and Standards

standard	CSA C22.2 #188, 486C/467 UL Listed, RoHS
Temperature Rating	105 DEG C Shell Rated