



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 301263J Weatherproof Wire Conn, 63 Gray/DK Blue, 50/Jar

*Ideal*

Catalog Number	301263J
Manufacturer	Ideal
Description	Model 63 Gray Blue 50 Jar
Weight per unit	0.0260 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

### Features

Quantity	Jar of 50
----------	-----------

### Material, Color, and Finish

Color	Gray
-------	------

### Descriptions

Description	WEATHERPROOF WIRE CONN, 63 GRAY/DK BLUE, 50/JAR
extra long description	IDEAL 30-1263J WP MODEL 63 GRAY BLU
Features	100% Silicone-based sealant protects against moisture and corrosionUL Listed to 486G Sealed Twist-On Wire Connector for use in damp/wet locations or above-grade applicationsEasy to apply, pre-filled twist-on wire connectorsSwept wing design is built for comfort and efficiencyEliminates the need for heat-shrink or excessive tapingTough, UL 94V-2 flame-retardant shell rated at 105°C (221°F)Models 61 and 63 approved for bonding and grounding applicationsFor use in damp/wet location or above-grade applications
Long Description	MODEL 63 GRAY BLUE 50 JAR
Product Type	WP Model 63 Gray Blue 50 Jar
Special Features	Silicone-based sealant protects against moisture and corrosion. Easy to apply pre-filled twist-on wire connectors

### Manufacturer Information

Brand	Ideal
GTIN	00783250756377
Manufacturers Part Number	30-1263J
UPC	783250756377

### Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
Type	Model 63® Connector

### Availability

minimum qty	50
-------------	----



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton ..... 50

Weight Per each ..... 0.026

## Uses, Certifications, and Standards

Application ..... Handles wire sizes from #16 to #6 AWG copper. Minimum of 3  
#14 AWG. Maximum of 2 #8 & 1 #10 AWG

standard ..... UL listed for 486D for use in damp/wet locations