



## 30190S

F40T12 BL (PK X 15)



**Application:** Industrial, Food Processing, Food Service, Retail, Hospitality, General Lighting

**Base:** Medium Bi-Pin (G13)

**Coating:** Copolymer

**Diameter:** 1.50 IN

**Length:** 48.00 IN

**Package Weight:** 13.40 L

**Shape:** T

**Type:** Straight Linear Fluorescent Lamp

**Wattage:** 40.0 W

**Average Life Hours:** 20000

**Bulb:** T12

**Color:** Black Light

**Lamp Type:** Fluorescent

**Package (LxWxH):** 49.25 IN x 5.50 IN x 8.75 IN

**Pack By:** 15

**Special Features:** Shatter-Resistant

**UPC:** 726585301904

ULEPH,ROHS,NSF Splash Zone



## 30190S

F40T12 BL (PK X 15)



**Application:** Industrial, Food Processing, Food Service, Retail, Hospitality, General Lighting

**Base:** Medium Bi-Pin (G13)

**Coating:** Copolymer

**Diameter:** 1.50 IN

**Length:** 48.00 IN

**Package Weight:** 13.40 L

**Shape:** T

**Type:** Straight Linear Fluorescent Lamp

**Wattage:** 40.0 W

**Average Life Hours:** 20000

**Bulb:** T12

**Color:** Black Light

**Lamp Type:** Fluorescent

**Package (LxWxH):** 49.25 IN x 5.50 IN x 8.75 IN

**Pack By:** 15

**Special Features:** Shatter-Resistant

**UPC:** 726585301904

ULEPH,ROHS,NSF Splash Zone