



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

303470 Non-GRND STRND Wire Pigtail-#10 FRK/Strip, 25/Bag

Ideal

Catalog Number	303470
Manufacturer	Ideal
Description	Ideal, Wire Connector, Pigtail, Size: 8 In Length, Wire Size: 12 Awg, Material: Brass-Alloy, Color: White, Wire Type: Stranded, Includes: #10 Fork and Stripped End
Weight per unit	0.0180 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Brass-Alloy
Wire Size	12
Wire Type	STRANDED

Material, Color, and Finish

Color	White
-------	-------

Dimensions and Weight

Size	8 IN Length
------	-------------

Descriptions

Description	NON-GRND STRND WIRE PIGTAIL-#10 FRK/STRIP, 25/BAG
extra long description	IDEAL 30-3470 Wire Connector, Ideal,
Long Description	IDEAL, Wire Connector, Pigtail, Size: 8 IN Length, Wire Size: 12 AWG, Material: Brass-Alloy, Color: White, Wire Type: Stranded, Includes: #10 Fork And Stripped End
Product Type	Wire Connector, Ideal, P/T, SZ: 8.000 In Len, Wire SZ: 12 Awg, BR
Special Features	Features: Ultra-Flexible 8 IN Lead Allows For Easy Positioning In Outlet Box - Reduces Stress On Device, Wires And Connection; Brass-Alloy Terminals With Locking Tabs For Fast, Efficient Device Connection; Includes: #10 Fork And Stripped End

Manufacturer Information

Brand	Ideal
GTIN	00783250697533
Manufacturers Part Number	30-3470
UPC	783250697533

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	PIGTAIL

Availability

minimum qty	25
-------------	----



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	25
Package	250
Weight Per each	0.018

Uses, Certifications, and Standards

Application	For Easy Positioning In Outlet Box - Reduces Stress On Device, Wires And Connection And Fast, Efficient Device Connection
standard	RoHS