



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



30826 1800W 120V Photo Cell *Mulberry Metal*

| | |
|------------------|---|
| Catalog Number | 30826 |
| Manufacturer | Mulberry Metal |
| Description | Mulberry; Photo Control; Direct Wire-In; Supply Voltage: 120 V; Timing Range: 15 S; Connection: 1/2-14 In Threaded Stem; Mounting: Fixed or Swivel; Enclosure: High Impact Polycarbonate; Operating Temperature: -40 to 158 Deg F; Tungsten Watts: 1800 WTT; Tungsten Amps: 15 Amp; Ballast Watts: 1000 WTT; Ballast Amps: 8.3 Amp |
| Weight per unit | 0.3800 (lbs/each) |
| Product Category | Lighting Photocells |

Features

| | |
|----------------|-------------------------|
| connection | 1/2-14 IN Threaded Stem |
| supply voltage | 120 |
| Timing Range | 15 |

Descriptions

| | |
|------------------------|--|
| Description | 1800W 120V PHOTO CELL |
| extra long description | MULB 30826 120V SWIVEL PHOTO CONTRO |
| Long Description | Mulberry; Photo Control; Direct Wire-In; Supply Voltage: 120 V; Timing Range: 15 S; Connection: 1/2-14 IN Threaded Stem; Mounting: Fixed Or Swivel; Enclosure: High Impact Polycarbonate; Operating Temperature: -40 To 158 DEG F; Tungsten Watts: 1800 WTT; Tungsten Amps: 15 AMP; Ballast Watts: 1000 WTT; Ballast Amps: 8.3 AMP |
| Product Type | 120V Swivel Photo Control |
| Special Features | Features: High Impact Polycarbonate Housing; Turn On Between 1 And 5 Foot Candles; Turn On/Turn Off Ratio 1 To 3; Single-Pole, Single-Throw Switching; Minimum Time Delay 15 Seconds; Contact Position At Night Normally Closed; External Slide Clip Allows Light Level Adjustment; With 2 IN - 14 Threaded Stem Fits 2 IN Knockout; With 6 IN Color-Coded Lead Wire; Temperature Range -40 Deg F (-40 Deg C) To 158 Deg F (70 Deg C); Tungsten Watts: 1800 WTT; Tungsten Amps: 15 AMP; Ballast Watts: 1000 WTT; Ballast Amps: |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Mulberry |
| GTIN | 00095327308267 |
| Manufacturers Part Number | 30826 |
| UPC | 095327308267 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | Commercial dimmers, motion sensors, & photo cells |
| Type | Direct Wire-In |

Availability

| | |
|--------|----------|
| Status | Inactive |
|--------|----------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.38 |

Uses, Certifications, and Standards

| | |
|-----------------------|---------------------------|
| Application | For Wet Locations |
| Enclosure | High Impact Polycarbonate |
| Mounting | Fixed Or Swivel |
| Operating Temperature | -40 to 158 |
| standard | UL Listed, CSA Certified |