



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



30AC2I 30A 120/277VAC B+S Wire DP SW Iv

Pass & Seymour/Legrand

| | |
|------------------|--|
| Catalog Number | 30AC2I |
| Manufacturer | Pass & Seymour/Legrand |
| Description | 2-Pole Toggle Switch, Back and Side-Wire, 30A 120/277V |
| Weight per unit | 0.2170 (lbs/each) |
| Product Category | Gen Purpose Switches |

Features

| | |
|-----------------|-------------------|
| action | Double pole |
| amperage rating | 30 |
| Contact Rating | 30Amp, 120/277Vac |
| insulation | False |
| Poles | Double Pole |
| Switch Type | Toggle |
| Voltage | 120.0 V |
| Voltage Rating | 120/277 |

Dimensions and Weight

| | |
|------|--------|
| Size | 3.3 in |
|------|--------|

Descriptions

| | |
|------------------------|--|
| Description | 30A 120/277VAC B+S WIRE DP SW IV |
| extra long description | P&S PS30AC2I 30A 120/277VAC B+S WIR |
| Long Description | 2-Pole Toggle Switch, Back and Side-Wire, 30A 120/277V |
| Product Type | 30A 120/277VAC B+S Wire DP SW I |
| Special Features | Back & side wire, locking support, heavy duty toggle |

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007195552 |
| Manufacturers Part Number | PS30AC2I |
| UPC | 785007195552 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------|
| Category Description | Industrial switches |
| Type | TOGGLE SWITCH |

Trade Size

| | |
|----------|------|
| Amperage | 30.0 |
|----------|------|

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.217 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|---------------------------|
| Application | Industrial Spec Grade |
| Enclosure | Nylon |
| Mounting | WALL |
| standard | CULUS, FEDSPEC, UL 498/20 |