

# TradeMaster Receptacle

3232LA



Duplex Grounding Receptacle made with high-impact resistant thermoplastic construction and long-term blade retention. It has ultrasonic welding of face to back body. 15 amp, 125 volt, Light Almond.

## features & benefits

- Extra-long strap. Quickloop wire looping aid. Longer tri-drive screws for easier #12 AWG looping.
- Extra-large circuit break-off tabs. Side-access push wire release. Side wire accepts #12 - #14 AWG solid wire. Push wire accepts #14 AWG solid only.
- Low profile face. Traditional contoured face. (3232 models) Self-grounding models provide automatic ground clip.

## specifications

### General Info

Color: Light Almond  
Number Of Poles: 2  
Number Of Wires: 3

### Listing Agencies/Third Party Information

CSA Listing Info: C22.2 No.42  
CSA Standard: Yes  
Federal Spec: No  
UL Listing No: UL498  
UL Standard: Yes  
UN SPS C: 39121406

### Dimensions

Depth U S: 0.96"  
Height U S: 3.31"  
Width U S: 1.32"

**Technical Information**

Amps: 15  
Volts: 125  
Volts A C: 125

**Buy American Act Compliance**

Country of Origin: CHINA  
Buy American Act Status: No