



Pass and Seymour
Trademaster® 15A/125V Duplex Receptacle, White
Part No. 3232W



Our Pass and Seymour TradeMaster® receptacles combine a traditional look with reliable, time-tested operation for any residential application.

Features & Benefits

Durable, high-quality construction

125-volt outlet

Wire Size: #12 - #14 AWG, Solid wire

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007323276
Country Of Origin	China	Number of Receptacles	2
Features	Extra Long Strap	Outlet Type	Straight Blade
Application Sector	Hospitality, Residential	Wall Plate Included	No
Standard	UL 498	Warranty Type	1-Year Limited Warranty

Dimensions

Product Width US	1.32 in	Product Depth US	1.0 in
Product Height US	3.31 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

Product Environmental Profile Yes

Technical Information

Connection Location	Side Only	Number of Wires	3
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 12 AWG	Indoor/Outdoor	Indoor
Voltage	125.0 V		



Pass and Seymour
Trademaster® 15A/125V Duplex Receptacle, White
Part No. 3232W



Our Pass and Seymour TradeMaster® receptacles combine a traditional look with reliable, time-tested operation for any residential application.

Features & Benefits

Durable, high-quality construction	125-volt outlet
Wire Size: #12 - #14 AWG, Solid wire	

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007323276
Country Of Origin	China	Number of Receptacles	2
Features	Extra Long Strap	Outlet Type	Straight Blade
Application Sector	Hospitality, Residential	Wall Plate Included	No
Standard	UL 498	Warranty Type	1-Year Limited Warranty

Dimensions

Product Width US	1.32 in	Product Depth US	1.0 in
Product Height US	3.31 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

Product Environmental Profile Yes

Technical Information

Connection Location	Side Only	Number of Wires	3
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 12 AWG	Indoor/Outdoor	Indoor
Voltage	125.0 V		
