



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 3801 STR Blade Recept 2P 3W 30a

*Pass & Seymour/Legrand*

|                  |  |
|------------------|--|
| Catalog Number   | 3801   |
| Manufacturer     | Pass & Seymour/Legrand   |
| Description      | Straight Blade Receptacle, 30 A, 250 V Ac, 2 Poles, 3 Wires, Wire Ground Connection, Wall Mount, 2.5 In Length, 2.2 In Width, 3.75 In Height, Thermoplastic, Black, Arc Resistant, 0.3900 LB |
| Weight per unit  | 0.3904 (lbs/each)  |
| Product Category | Gen Purpose Recept & Surge Pro   |

### Features

|                 |             |
|-----------------|-------------|
| amperage rating | 30          |
| connection      | Wire Ground |
| Poles           | Double Pole |
| Voltage         | 250.0 V     |
| Wire Size       | 4           |

### Dimensions and Weight

|      |        |
|------|--------|
| Size | 3.8 in |
|------|--------|

### Descriptions

|                        |                                   |
|------------------------|-----------------------------------|
| Description            | STR BLADE RECP 2P 3W 30A          |
| extra long description | P&S 3801 STR BLADE RECP 2P 3W 30A |

### Manufacturer Information

|       |                  |
|-------|------------------|
| Brand | Pass and Seymour |
| GTIN  | 00785007380101   |
| UPC   | 785007380101     |

### Taxonomies, Classifications, and Categories

|                      |                           |
|----------------------|---------------------------|
| Category Description | Residential receptacles   |
| Type                 | Straight Blade Receptacle |

### Trade Size

|          |      |
|----------|------|
| Amperage | 30.0 |
|----------|------|

### Packaging

|                 |        |
|-----------------|--------|
| Carton          | 1      |
| Package         | 25     |
| Weight Per each | 0.3904 |

### Uses, Certifications, and Standards

|          |                        |
|----------|------------------------|
| Mounting | WALL                   |
| standard | CULUS, UL, CSA, UL 498 |