

Eaton 38B-BOX

Catalog Number: 38B-BOX

Eaton power device receptacle, Dryer, #12 - 4 AWG, 30A, Flush, 125/250V, Back, Brown, NEMA 10-30R, Three-pole, Three-wire, Three-pole, three-wire, non grounding, Screw, Glass-filled nylon, Power, Used with S80

General specifications

Product Name	Catalog Number
Eaton power device receptacle	38B-BOX
UPC	Product Length/Depth
032664199103	2.226 in
Product Height	Product Width
3.674 in	2.256 in
Product Weight	Compliances
0.26 lb	RoHS Compliant
	NAFTA
Certifications	
UL Listed	

Product specifications

Used with

S80

Special features

Dryer

Amperage Rating

30A

Voltage rating

125/250 V

Wiring method

Back

Number of wires

3

Mounting method

Flush

Number Of Poles

Three-pole

Color

Brown

Connection type

Screw

Style

Power

Allowable wire size

#12-4 AWG

NEMA configuration

10-30R

Torque rating

25 lbf-inch

Design type

Receptacle

Material

Glass filled nylon

Receptacle type

Three-pole, three-wire, non grounding

Resources

Brochures

[Flush mount receptacles sell sheet](#)

Catalogs

[Arrow Hart Buyers Guide Section B](#)

Specifications and datasheets

[Eaton Specification Sheet - 38B-BOX](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton 38B-BOX

Catalog Number: 38B-BOX

Eaton power device receptacle, Dryer, #12 - 4 AWG, 30A, Flush, 125/250V, Back, Brown, NEMA 10-30R, Three-pole, Three-wire, Three-pole, three-wire, non grounding, Screw, Glass-filled nylon, Power, Used with S80

General specifications

Product Name	Catalog Number
Eaton power device receptacle	38B-BOX
UPC	Product Length/Depth
032664199103	2.226 in
Product Height	Product Width
3.674 in	2.256 in
Product Weight	Compliances
0.26 lb	RoHS Compliant
	NAFTA
Certifications	
UL Listed	



Product specifications

Used with

S80

Special features

Dryer

Amperage Rating

30A

Voltage rating

125/250 V

Wiring method

Back

Number of wires

3

Mounting method

Flush

Number Of Poles

Three-pole

Color

Brown

Connection type

Screw

Style

Power

Allowable wire size

#12-4 AWG

NEMA configuration

10-30R

Torque rating

25 lbf-inch

Design type

Receptacle

Material

Glass filled nylon

Receptacle type

Three-pole, three-wire, non grounding

Resources

Brochures

[Flush mount receptacles sell sheet](#)

Catalogs

[Arrow Hart Buyers Guide Section B](#)

Specifications and datasheets

[Eaton Specification Sheet - 38B-BOX](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)