



Powering Business Worldwide

### 3962-BU

Cover 1G Dup Recp Wet Loc Hor Plas GY

UPC: 032664455414

Brand Name: Eaton  
Sub Brand: ARROW HART  
Type: Straight Blade  
Special Features: Angled Body, Grounding  
Application: Industrial  
Number Of Poles: 2  
Number Of Wires: 3  
Wire Size: 18 To 12 AWG  
Amperage Rating: 15 Amp  
Voltage Rating: 125 Vac  
Cord Type: 0.25 To 0.69 In Diameter  
Material: Polycarbonate  
Color: Black, White  
NEMA Rating: 5-15P  
Connection: Screw  
Size: 1.42 In Length X 1.25 In Width X 1.95 In Depth  
Environmental Conditions: -40 To 75 Deg C

### 3962W-BU

Cover 1G Dup Recp Wet Loc Hor Plas WH

UPC: 032664543081

Brand Name: Eaton  
Sub Brand: ARROW HART  
Type: Straight Blade  
Special Features: Angled Body, Grounding  
Application: Industrial  
Number Of Poles: 2  
Number Of Wires: 3  
Wire Size: 18 To 12 AWG  
Amperage Rating: 20 Amp  
Voltage Rating: 125 Vac  
Cord Type: 0.25 To 0.69 In Diameter  
Material: Polycarbonate  
Color: Black, White  
NEMA Rating: 5-20P  
Connection: Screw  
Size: 1.51 In Diameter  
Environmental Conditions: -40 To 75 Deg C