



**Product Number:** 16104

**Order Abbreviation:** 39PAR20/HAL/FL30 120V

**General Description:** Tungsten Halogen PAR20 Reflector Lamp 39Watt 120Volt Medium Base Flood30 Beam

**\* Full Case Required**

#### Product Information

Abbrev. With Packaging Info.	39PAR20HALFL30 120V 10/CS 1/SKU
Approx. Lumens	475
Average Rated Life (hr)	1500
Base	E26 Medium
Beam Angle (deg)	30
Beam Type	FL
Bulb	PAR20
Centerbeam Candlepower (cp)	1000
Class	C (gas)
Color Rendering Index (CRI)	100
Color Temperature/CCT (K)	2850
Diameter (in)	2.500
Diameter (mm)	63.50
Ecologic	Yes
Family Brand Name	Halogen Par20
Filament	CC-8
Horizontal Beam Angle (deg)	30
Lamp Finish	Reflector
Maximum Overall Length - MOL (in)	3.25
Maximum Overall Length - MOL (mm)	79.375
Nominal Voltage (V)	120.00
Nominal Wattage (W)	39.00
Vertical Beam Angle (deg)	30



ECOLOGIC  
TM



#### Footnotes

- State of the Art SPL Optics
- In base up operation, heat may eventually deteriorate paper-lined or plastic sockets.