



Powering Business Worldwide

pe.eaton.com

BR style 1-inch commercial loadcenter

3BR3030N100

UPC:786676442909

Dimensions:

- **Height:** 29.13 IN
- **Length:** 3.88 IN
- **Width:** 14.31 IN

Notes:The maximum rating of the panel is the main breaker rating when used as service entrance equipment. Has notch for brhdk125 hold-down kit.

Warranties:

- 10 year

Specifications:

- **Special Features:** No feed-thru lugs, includes BREQS125 hold-down screw
- **Type:** Convertible main
- **Amperage Rating:** 100A
- **Box Size:** D1
- **Bus Material:** Aluminum
- **Cover:** Cover included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 10 kAIC
- **Main Circuit Breaker:** BR
- **Mounting:** Combination
- **Number Of Circuits:** 30
- **Number Of Wires:** Four-wire
- **Phase:** Three-phase
- **Used With:** Type BR 1-inch breakers
- **Voltage Rating:** 208Y/120, 240V
- **Wire Size:** Determined by circuit breaker installed

Supporting documents:



- Dimensional Drawing - BR 1 LOADCENTER, BR CONVERTIBLE, INDOOR NEMA 1, 120/240 VAC, 3 PHASE
- Eatons Volume 1-Residential and Light Commercial
- Type BR 3-Phase Loadcenters
- 3-Phase Loadcenter Program

Certifications:

- UL 67
- UL 50

Product compliance: No Data