

Specifications



Eaton 3MCB1000R

Eaton main circuit breaker, 1000A, Aluminum, NEMA 3R, Overhead/underground, 65 kAIC, NGS, Four-wire, Three-phase, 120/208V, (4) #4/0 AWG-500 kcmil

General specifications

PRODUCT NAME	Eaton main circuit breaker
CATALOG NUMBER	3MCB1000R
UPC	782116008278
PRODUCT LENGTH/DEPTH	13.8 in
PRODUCT HEIGHT	39.4 in
PRODUCT WIDTH	27 in
PRODUCT WEIGHT	160 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed
CATALOG NOTES	Neutral lugs order 1MCB1200NLK. Main devices with a rating greater than 800A can be used with 800A residential modular stacks, but only as a center fed main.

Product specifications

AMPERAGE RATING	1000 A
BUS MATERIAL	Aluminum
FEED TYPE	Top/bottom
PHASE	Three-phase
VOLTAGE RATING	120/208 V
UTILITY APPROVALS	MI : DTE Energy (Detroit Edison) MD : Baltimore Gas and Electric DC : PEPCO MD : PEPCO NC : Dominion VA : Dominion
ENCLOSURE	NEMA 3R
INTERRUPT RATING	65 kAIC
MAIN CIRCUIT BREAKER	NGS
NUMBER OF WIRES	4
WIRE SIZE	(4) #4/0 AWG-500 kcmil

Resources

CATALOGS	Residential and Light Commercial, Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - 3MCB1000R

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Eaton 3MCB1000R

Eaton main circuit breaker, 1000A, Aluminum, NEMA 3R, Overhead/underground, 65 kAIC, NGS, Four-wire, Three-phase, 120/208V, (4) #4/0 AWG-500 kcmil

General specifications

PRODUCT NAME	Eaton main circuit breaker
CATALOG NUMBER	3MCB1000R
UPC	782116008278
PRODUCT LENGTH/DEPTH	13.8 in
PRODUCT HEIGHT	39.4 in
PRODUCT WIDTH	27 in
PRODUCT WEIGHT	160 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed
CATALOG NOTES	Neutral lugs order 1MCB1200NLK. Main devices with a rating greater than 800A can be used with 800A residential modular stacks, but only as a center fed main.

Product specifications

AMPERAGE RATING	1000 A
BUS MATERIAL	Aluminum
FEED TYPE	Top/bottom
PHASE	Three-phase
VOLTAGE RATING	120/208 V
UTILITY APPROVALS	MI : DTE Energy (Detroit Edison) MD : Baltimore Gas and Electric DC : PEPCO MD : PEPCO NC : Dominion VA : Dominion
ENCLOSURE	NEMA 3R
INTERRUPT RATING	65 kAIC
MAIN CIRCUIT BREAKER	NGS
NUMBER OF WIRES	4
WIRE SIZE	(4) #4/0 AWG-500 kcmil

Resources

CATALOGS	Residential and Light Commercial, Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - 3MCB1000R

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

