








# Metal Raceway HBL2400 and HBL2400D Series

*Metal Raceway, Device Boxes, Elbows and Tees*

HBL2400 Series	Description	Color	Catalog Number
	<b>Undivided Base and Cover</b> Packed 50 ft. (15m) per carton, 5 ft. (1.5m) lengths.	Ivory	<b>HBL2400BCIV</b> A: 60.00" (1,524.00) B: 1.91" (48.51) C: .88" (22.40)





HBL2400 Series Base and Cover	Description	Color	Catalog Number	HBL2400D Series Base and Cover	Description	Color	Catalog Number
	<b>10 Ft. Base, Undivided</b> Packed 100 ft. (30.5m) per carton, 10 ft. (3m) lengths.	Ivory	<b>HBL2400B10IV</b> A: 120.00" (3,048.00) B: 1.91" (48.51)		<b>5 Ft. Cover</b> Packed 50 ft. (15m) per carton, 5 ft. (1.5m) lengths.	Ivory	<b>HBL2400CIV</b> A: 60.00" (1,524.00) B: 1.89" (48.00)
	<b>5 Ft. Base, Undivided</b> Packed 50 ft. (15m) per carton, 5 ft. (1.5m) lengths.	Ivory	<b>HBL2400BIV</b> A: 60.00" (1,524.00) B: 1.91" (48.51)				
	<b>10 Ft. Base, Divided</b> Packed 100 ft. (30.5m) per carton, 10 ft. (3m) lengths.	Ivory	<b>HBL2400BDIV</b> A: 120.00" (3,048.00) B: 1.91" (48.51)				



Standard	Extra Deep	Description	Color	Type	1-Gang	2-Gang
		<b>Device Box</b> For deep switches and receptacles. Base has one 1/2 in. trade size KO and rectangular KO for extension to wall box.	Ivory Ivory	Divided Undivided	— <b>HBL2448IV</b> A: 4.54" (115.32) B: 2.82" (71.63) C: 1.75" (44.45)	— <b>HBL24482IV</b> A: 4.54" (115.32) B: 4.64" (117.86) C: 1.75" (44.45)
		<b>Device Box</b> For deep switches and receptacles. Base has one 1/2 in. trade size KO and rectangular KO for extension to wall box (undivided box pictured).	Ivory Ivory	Divided Undivided	<b>HBL2444DIV</b> <b>HBL2444IV</b> A: 4.54" (115.32) B: 2.82" (71.63) C: 2.75" (69.85)	<b>HBL2444D2AIV</b> <b>HBL24442IV</b> A: 4.54" (115.32) B: 4.64" (117.86) C: 2.75" (69.85)

Elbows and Tees	Description	Color	Type	Catalog Number	Description	Color	Type	Catalog Number
	<b>Internal Elbow Bend Radius</b> For inside surfaces at right angles, requiring a 1.5 in. (38.10) bend radius. Suitable for Category 5, 5e, 6 and 6a applications.	Ivory Ivory	Divided Undivided	<b>HBL2417DFOIV*</b> <b>HBL2417IV**</b> A: 1.91" (48.51) B: 3.60" (91.30)	<b>External Elbow Bend Radius</b> For right angle turns around external corners. Suitable for Category 5, 5e, 6 and 6a applications.	Ivory Ivory	Divided Undivided	<b>HBL2418DFOIV*</b> <b>HBL2418IV**</b> A: 1.91" (48.51) B: 3.83" (97.28)
	<b>90° Flat Elbow Bend Radius</b> For right angle turns on same surface. Suitable for Category 5, 5e, 6 and 6a applications.	Ivory Ivory	Divided Undivided	<b>HBL2411DFOIV*</b> <b>HBL2411IV**</b> A: 6.00" (152.40) B: 5.00" (127.00) C: .90" (22.86)	<b>Tee Fitting Bend Radius</b> For branches at right angles. Suitable for Category 5, 5e, 6 and 6a applications.	Ivory Ivory	Divided Undivided	<b>HBL2415DFOIV*</b> <b>HBL2415IV**</b> A: 7.30" (185.42) B: 4.99" (126.75) C: 1.44" (36.58)



Note: \* HBL2401DC couplings included.  
\*\* HBL2401C couplings included.

