



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



408DC12 3/4" Ins Diecast Squeeze Connector *Bridgeport Fittings*

| | |
|------------------|---|
| Catalog Number | 408DC12 |
| Manufacturer | Bridgeport Fittings |
| Description | Connector, Squeeze, Zinc Die Cast, Insulated Throat, Trade Size 3/4 Inch |
| Weight per unit | 0.1290 (lbs/each) |
| Product Category | Liquid Tight Fittings |

Features

| | |
|----------------|--------------------|
| angle | 180 Deg |
| Connector Type | Squeeze, Insulated |
| Material | Zinc Die Cast |
| media | Yes |

Material, Color, and Finish

| | |
|--------|--------------|
| Finish | Ball burnish |
|--------|--------------|

Dimensions and Weight

| | |
|------|-----|
| Size | 3/4 |
|------|-----|

Descriptions

| | |
|------------------------|---|
| Description | 3/4" INS DIECAST SQUEEZE CONNECTOR |
| extra long description | BPT 408-DC12 3/4" SQUEEZE CONN. INS |
| Long Description | Connector, Squeeze, Zinc Die Cast, Insulated Throat, Trade Size 3/4 Inch |
| Product Type | 3/4" Squeeze Conn. Ins. Zinc |
| Special Features | Furnished with Tri-Drive screw |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Bridgeport |
| GTIN | 00781747164087 |
| Manufacturers Part Number | 408-DC12 |
| UPC | 781747164087 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------|
| Category Description | FLEX & MC FITTINGS |
| Type | CONNECTOR |

Trade Size

| | |
|------------|-----|
| Trade Size | 3/4 |
|------------|-----|

Packaging

| | |
|-----------------|-------|
| Carton | 25 |
| Package | 100 |
| Weight Per each | 0.129 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------|--|
| Application | Used to connect steel flexible metal conduit or XRW FMC to box or enclosure. Insulator rated 105 degree C. |
| standard | UL |
| Temperature Rating | 105°C |