

InstaBright Armor Coat covered CFLs

8,000 Hours average rated life, 120Volts

Applications:

Instantly bright! Use where a standard incandescent is used.

- + Table Lamps
- + Floor Lamps
- + Ceiling Fixtures
- + Wall Sconces
- + Vanities
- + Recessed Cans
- + Track Lighting



Features and Benefits




InstaBright

- Fastest starting covered CFL reaches full brightness in seconds
- Fast run-up time and build-up time, lamps turns on instantly
- Patented technology using amalgam mercury
- RoHS Compliant
- Huge breakthrough in CFL technology!




Armor Coat

- Durable coating keeps glass and bulb contents contained with no loss of light output.




TCP is brighter faster!




Specifications (at full brightness)


| | |
|------------------------------|------------|
| End of Life Protection | Yes |
| Ballast Type | Electronic |
| Input Line Voltage: | 120VAC |
| Input Line Frequency | 50/60HZ |
| Lamp Life (Rated) | 8,000 hrs |
| Color Temperature | 2700°K |
| Color Rendering Index | 82 |
| Minimum Starting Temp | -20°F |
| Maximum Operating Temp | 160°F |
| UL/cUL Listed | Yes |
| Lamp Operating Frequency | 45 KHZ |
| Lamp Current Crest Factor | <1.60 |
| Maximum Open Circuit Voltage | 600V |
| Power Factor | >.50 |
| Total Harmonic Distortion | <150% |




4R3014A



4G2514A



4R2014A



4I314A

Complete product listing on back

| Warranties and Certifications: | Item # | Description | Incandescent Wattage Comparison | Initial Lumens | M.O.L. (inches) | Diameter (inches) | Lamp Life (Hours) |
|--|---------|--|---------------------------------|----------------|-----------------|-------------------|-------------------|
| 12 MONTH WARRANTY RoHS Compliant ISO 9002 CERTIFIED | 4R2014A | 14 WATT R20 InstaBright G2 with Armor Coat | 50 | 410 | 4.4 | 2.5 | 8,000 |
| | 4R3014A | 14 WATT R30 InstaBright G2 with Armor Coat | 65 | 650 | 5.4 | 3.7 | 8,000 |
| | 4I314A | 14 WATT A19 InstaBright G2 with Armor Coat | 75 | 800 | 4.4 | 2.4 | 8,000 |
| | 4G2514A | 14 WATT G25 InstaBright G2 with Armor Coat | 100 | 800 | 4.4 | 3.1 | 8,000 |



| Item # | Description | Color Temperature (°K) | Incandescent Wattage Comparison | Initial Lumens | M.O.L. (inches) | Diameter (inches) | Lamp Life (Hours) |
|------------|---|------------------------|---------------------------------|----------------|-----------------|-------------------|-------------------|
| 4R2014A | 14 WATT R20 InstaBright G2 with Armor Coat | 27K | 50 | 410 | 4.4 | 2.5 | 8,000 |
| 4R2014A30K | 14 WATT R20 InstaBright G2 with Armor Coat 30K | 30K | 50 | 410 | 4.4 | 2.5 | 8,000 |
| 4R2014A35K | 14 WATT R20 InstaBright G2 with Armor Coat 35K | 35K | 50 | 380 | 4.4 | 2.5 | 8,000 |
| 4R2014A41K | 14 WATT R20 InstaBright G2 with Armor Coat 41K | 41K | 50 | 380 | 4.4 | 2.5 | 8,000 |
| 4R2014A50K | 14 WATT R20 InstaBright G2 with Armor Coat 50K | 50K | 50 | 380 | 4.4 | 2.5 | 8,000 |
| 4R3014A | 14 WATT R30 InstaBright G2 with Armor Coat | 27K | 65 | 650 | 5.4 | 3.7 | 8,000 |
| 4R3014A30K | 14 WATT R30 InstaBright G2 with Armor Coat 30K | 30K | 65 | 650 | 5.4 | 3.7 | 8,000 |
| 4R3014A35K | 14 WATT R30 InstaBright G2 with Armor Coat 35K | 35K | 65 | 600 | 5.4 | 3.7 | 8,000 |
| 4R3014A41K | 14 WATT R30 InstaBright G2 with Armor Coat 41K | 41K | 65 | 600 | 5.4 | 3.7 | 8,000 |
| 4R3014A50K | 14 WATT R30 InstaBright G2 with Armor Coat 50K | 50K | 65 | 600 | 5.4 | 3.7 | 8,000 |
| 41314A | 14 WATT A-Lamp InstaBright G2 with Armor Coat | 27K | 60 | 800 | 4.4 | 2.4 | 8,000 |
| 41314A30K | 14 WATT A-Lamp InstaBright G2 with Armor Coat 30K | 30K | 60 | 800 | 4.4 | 2.4 | 8,000 |
| 41314A35K | 14 WATT A-Lamp InstaBright G2 with Armor Coat 35K | 35K | 60 | 750 | 4.4 | 2.4 | 8,000 |
| 41314A41K | 14 WATT A-Lamp InstaBright G2 with Armor Coat 41K | 41K | 60 | 750 | 4.4 | 2.4 | 8,000 |
| 41314A50K | 14 WATT A-Lamp InstaBright G2 with Armor Coat 50K | 50K | 60 | 750 | 4.4 | 2.4 | 8,000 |
| 4G2514A | 14 WATT G25 InstaBright G2 with Armor Coat | 27K | 60 | 800 | 4.4 | 3.1 | 8,000 |
| 4G2514A30K | 14 WATT G25 InstaBright G2 with Armor Coat 30K | 30K | 60 | 800 | 4.4 | 3.1 | 8,000 |
| 4G2514A35K | 14 WATT G25 InstaBright G2 with Armor Coat 35K | 35K | 60 | 750 | 4.4 | 3.1 | 8,000 |
| 4G2514A41K | 14 WATT G25 InstaBright G2 with Armor Coat 41K | 41K | 60 | 750 | 4.4 | 3.1 | 8,000 |
| 4G2514A50K | 14 WATT G25 InstaBright G2 with Armor Coat 50K | 50K | 60 | 750 | 4.4 | 3.1 | 8,000 |

12 MONTH WARRANTY

RoHS
Compliant

ISO 9002
CERTIFIED



InstaBright Armor Coat covered CFLs

8,000 Hours average rated life, 120Volts

Applications:

Instantly bright! Use where a standard incandescent is used.

- + Table Lamps
- + Floor Lamps
- + Ceiling Fixtures
- + Wall Sconces
- + Vanities
- + Recessed Cans
- + Track Lighting



Features and Benefits




InstaBright

- Fastest starting covered CFL reaches full brightness in seconds
- Fast run-up time and build-up time, lamps turns on instantly
- Patented technology using amalgam mercury
- RoHS Compliant
- Huge breakthrough in CFL technology!




Armor Coat

- Durable coating keeps glass and bulb contents contained with no loss of light output.




TCP is brighter faster!




Specifications (at full brightness)


| | | |
|------------------------------|-------|------------|
| End of Life Protection | | Yes |
| Ballast Type | | Electronic |
| Input Line Voltage: | | 120VAC |
| Input Line Frequency | | 50/60HZ |
| Lamp Life (Rated) | | 8,000 hrs |
| Color Temperature | | 2700°K |
| Color Rendering Index | | 82 |
| Minimum Starting Temp | | -20°F |
| Maximum Operating Temp | | 160°F |
| UL/cUL Listed | | Yes |
| Lamp Operating Frequency | | 45 KHZ |
| Lamp Current Crest Factor | | <1.60 |
| Maximum Open Circuit Voltage | | 600V |
| Power Factor | | >.50 |
| Total Harmonic Distortion | | <150% |




4R3014A



4G2514A



4R2014A



41314A

Complete product listing on back

| Warranties and Certifications: | Item # | Description | Incandescent Wattage Comparison | Initial Lumens | M.O.L. (inches) | Diameter (inches) | Lamp Life (Hours) |
|--|---------|--|---------------------------------|----------------|-----------------|-------------------|-------------------|
| 12 MONTH WARRANTY RoHS Compliant ISO 9002 CERTIFIED | 4R2014A | 14 WATT R20 InstaBright G2 with Armor Coat | 50 | 410 | 4.4 | 2.5 | 8,000 |
| | 4R3014A | 14 WATT R30 InstaBright G2 with Armor Coat | 65 | 650 | 5.4 | 3.7 | 8,000 |
| | 41314A | 14 WATT A19 InstaBright G2 with Armor Coat | 75 | 800 | 4.4 | 2.4 | 8,000 |
| | 4G2514A | 14 WATT G25 InstaBright G2 with Armor Coat | 100 | 800 | 4.4 | 3.1 | 8,000 |



| Item # | Description | Color Temperature (°K) | Incandescent Wattage Comparison | Initial Lumens | M.O.L. (inches) | Diameter (inches) | Lamp Life (Hours) |
|------------|---|------------------------|---------------------------------|----------------|-----------------|-------------------|-------------------|
| 4R2014A | 14 WATT R20 InstaBright G2 with Armor Coat | 27K | 50 | 410 | 4.4 | 2.5 | 8,000 |
| 4R2014A30K | 14 WATT R20 InstaBright G2 with Armor Coat 30K | 30K | 50 | 410 | 4.4 | 2.5 | 8,000 |
| 4R2014A35K | 14 WATT R20 InstaBright G2 with Armor Coat 35K | 35K | 50 | 380 | 4.4 | 2.5 | 8,000 |
| 4R2014A41K | 14 WATT R20 InstaBright G2 with Armor Coat 41K | 41K | 50 | 380 | 4.4 | 2.5 | 8,000 |
| 4R2014A50K | 14 WATT R20 InstaBright G2 with Armor Coat 50K | 50K | 50 | 380 | 4.4 | 2.5 | 8,000 |
| 4R3014A | 14 WATT R30 InstaBright G2 with Armor Coat | 27K | 65 | 650 | 5.4 | 3.7 | 8,000 |
| 4R3014A30K | 14 WATT R30 InstaBright G2 with Armor Coat 30K | 30K | 65 | 650 | 5.4 | 3.7 | 8,000 |
| 4R3014A35K | 14 WATT R30 InstaBright G2 with Armor Coat 35K | 35K | 65 | 600 | 5.4 | 3.7 | 8,000 |
| 4R3014A41K | 14 WATT R30 InstaBright G2 with Armor Coat 41K | 41K | 65 | 600 | 5.4 | 3.7 | 8,000 |
| 4R3014A50K | 14 WATT R30 InstaBright G2 with Armor Coat 50K | 50K | 65 | 600 | 5.4 | 3.7 | 8,000 |
| 41314A | 14 WATT A-Lamp InstaBright G2 with Armor Coat | 27K | 60 | 800 | 4.4 | 2.4 | 8,000 |
| 41314A30K | 14 WATT A-Lamp InstaBright G2 with Armor Coat 30K | 30K | 60 | 800 | 4.4 | 2.4 | 8,000 |
| 41314A35K | 14 WATT A-Lamp InstaBright G2 with Armor Coat 35K | 35K | 60 | 750 | 4.4 | 2.4 | 8,000 |
| 41314A41K | 14 WATT A-Lamp InstaBright G2 with Armor Coat 41K | 41K | 60 | 750 | 4.4 | 2.4 | 8,000 |
| 41314A50K | 14 WATT A-Lamp InstaBright G2 with Armor Coat 50K | 50K | 60 | 750 | 4.4 | 2.4 | 8,000 |
| 4G2514A | 14 WATT G25 InstaBright G2 with Armor Coat | 27K | 60 | 800 | 4.4 | 3.1 | 8,000 |
| 4G2514A30K | 14 WATT G25 InstaBright G2 with Armor Coat 30K | 30K | 60 | 800 | 4.4 | 3.1 | 8,000 |
| 4G2514A35K | 14 WATT G25 InstaBright G2 with Armor Coat 35K | 35K | 60 | 750 | 4.4 | 3.1 | 8,000 |
| 4G2514A41K | 14 WATT G25 InstaBright G2 with Armor Coat 41K | 41K | 60 | 750 | 4.4 | 3.1 | 8,000 |
| 4G2514A50K | 14 WATT G25 InstaBright G2 with Armor Coat 50K | 50K | 60 | 750 | 4.4 | 3.1 | 8,000 |

12 MONTH WARRANTY

RoHS Compliant

ISO 9002 CERTIFIED

