

4492	6"	7.461	.990	5.900	-
4491	5"	6.295	.976	4.920	-
449	4"	4.925	.687	3.788	4"- 8 TPI
448	3 1/2"	4.425	.675	3.323	3 1/2"- 8 TPI
447	3"	3.930	.680	2.865	3"- 8 TPI
446	2 1/2"	3.226	.678	2.280	2 1/2"- 8 TPI
445	2"	2.628	.550	1.948	2"- 11.5 TPI
444	1 1/2"	2.260	.488	1.513	1 1/2"- 11.5 TPI
443	1 1/4"	2.000	.485	1.304	1 1/4"- 11.5 TPI
442	1"	1.640	.492	1.020	1"- 11.5 TPI
441	3/4"	1.281	.365	.780	3/4"- 14 TPI
440	1/2"	1.045	.365	.595	1/2"- 14 TPI
PART NO.	TRADE SIZE	"A"	"B"	"C"	INTERNAL THREADS

