



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 44808 Adjustable Cable Lockout

*Ideal*

Catalog Number	44808
Manufacturer	Ideal
Description	Ideal, Cable Lockout, Adjustable, Material: Steel Cable, Thermoplastic Body, Insulation: Insulated, Size: 1/4 In, Length: 6 FT, Finish: Clear Vinyl Coating, Cable Type: Flexible Multi-Stranded
Weight per unit	0.6000 (lbs/each)
Product Category	Safety Equipment

### Features

insulation	Insulated
Material	Steel Cable, Thermoplastic Body

### Dimensions and Weight

Length	6
Size	1/4



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	ADJUSTABLE CABLE LOCKOUT
extra long description	IDEAL 44-808 ADJUSTABLE CABLE LOCKO
Features	Infinitely adjustable safety hasp and cableIdeal for multiple circuit breaker panels and side-by-side gate valve lockoutsFeed the cable end through the points to be locked out, then back through the lockout body. Cinch it tight to remove any slack with the patented locking feature.Tough, flexible multi-stranded 6 ft. 1/4 in. dia. steel cable is insulated with a clear vinyl coatingTough, lightweight, dielectric thermoplastic body withstands chemicals; performs effectively in extreme conditionsUp to four wor
Long Description	IDEAL, Cable Lockout, Adjustable, Material: Steel Cable, Thermoplastic Body, Insulation: insulated, Size: 1/4 IN, Length: 6 FT, Finish: Clear Vinyl Coating, Cable Type: Flexible Multi-Stranded
Product Type	Adjustable Cable Lockout
Special Features	Features: Infinitely Adjustable Safety Hasp And Cable; Ideal For Multiple Circuit Breaker Panels And Side-By-Side Gate Valve Lockouts; Feed The Cable End Through The Points To Be Locked Out, Then Back Through The Lockout Body. Cinch It Tight To Remove Any Slack With The Patented Locking Feature; Tough, Flexible Multi-Stranded 6 FT 1/4 IN Dia. Steel Cable Is Insulated With A Clear Vinyl Coating; Tough, Lightweight, Dielectric Xenoy® Thermoplastic Body Withstands Chemicals; Performs Effectively In Extreme Co

## Manufacturer Information

Brand	Ideal
GTIN	00783250448081
Manufacturers Part Number	44-808
UPC	783250448081

## Taxonomies, Classifications, and Categories

Category Description	SAFETY PRODUCTS
Type	ADJUSTABLE

## Packaging

Carton	1
Weight Per each	0.6

## Uses, Certifications, and Standards

standard	RoHS
----------	------