



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

37489 45th Street
74804-0000, OK Shawnee
Phone: 405-585-0428
Fax: 405-395-0336



45092 Stripmaster Wire Stripper, 10-22 Awg

Ideal

Catalog Number	45092
Manufacturer	Ideal
Description	Stripmaster Standard Wire Stripper, Size: 10 - 22 Awg, Cushion Grip Handle, Die-Cast Frame, Die-Cast Handle, Knife-Type Blade, Stripping Range: Up to 7/8 In, Strip Hole Size: 0.144 In For 10 Awg, 0.113 In For 12 Awg, 0.09 In For 14 Awg, 0.072 For 16 Awg, 0.061 For 18 Awg, 0.048 For 20 Awg, 0.048 For 22 Awg, For PVC Vinyl Insulations
Weight per unit	0.9000 (lbs/each)
Product Category	Strippers

Features

Handle Type	CUSHION GRIP
Material	Die-Cast Frame

Material, Color, and Finish

Handle Material	Die-Cast
-----------------	----------

Dimensions and Weight

Size	10 - 22
------	---------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

37489 45th Street
74804-0000, OK Shawnee
Phone: 405-585-0428
Fax: 405-395-0336

Descriptions

Description	STRIPMASTER WIRE STRIPPER, 10-22 AWG
extra long description	IDEAL 45-092 STM STD 10-22GA
Features	The versatile Stripmaster/Stripmaster Lite Wire Strippers are the standard of the industry. They incorporate a gripper that firmly holds the wire in a center-line position with the stripping hole. The lever action of the stripper offers a mechanical advantage that makes stripping easier. This aids in production applications and reduces operator fatigue. One squeeze strips the wire clean, up to a full 7/8 in. (22mm). The jaws are automatically held open to allow removal of the wire without damaging its end. This s
Long Description	Stripmaster Standard Wire Stripper, Size: 10 - 22 AWG, Cushion Grip Handle, Die-Cast Frame, Die-Cast Handle, Knife-Type Blade, Stripping Range: Up To 7/8 IN, Strip Hole Size: 0.144 IN For 10 AWG, 0.113 IN For 12 AWG, 0.09 IN For 14 AWG, 0.072 For 16 AWG, 0.061 For 18 AWG, 0.048 For 20 AWG, 0.048 For 22 AWG, For PVC Vinyl Insulations
Product Type	STM STD 10-22ga
Special Features	Cleanly strips wire up to 7/8 IN (22 MM); Eliminates nicking, cutting and fraying of wire; Knife-type blades; One-third less hand pressure for each strip; Precision-ground, knife-type blades provide clean, accurate stripping; Spring-action motion increases leverage and reduces operator fatigue; Sturdy die-cast frame provides long-term durability; Wire gripper holds wire centered in hole

Manufacturer Information

Brand	Ideal
GTIN	00783250450923
Manufacturers Part Number	45-092
UPC	783250450923

Taxonomies, Classifications, and Categories

Category Description	HAND TOOLS
Type	Standard Wire Stripper

Packaging

Carton	1
Weight Per each	0.9

Uses, Certifications, and Standards

Application	For PVC Vinyl Insulations
-------------	---------------------------