

Specifications



Eaton 4750

Eaton safety grip locking receptacle, #14-10 AWG, 15A, Industrial, 277V, Back and side wiring, Black, Brass, Duplex, L7-15, Two-pole, Three-wire, Glass-filled nylon

General specifications

PRODUCT NAME	Eaton Arrow Hart locking receptacle
CATALOG NUMBER	4750
UPC	040893682433
PRODUCT LENGTH/DEPTH	1.1 in
PRODUCT HEIGHT	6.5 in
PRODUCT WIDTH	3.5 in
PRODUCT WEIGHT	0.25 lb
COMPLIANCES	Federal Specifications Classification W-C375
CERTIFICATIONS	UL Listed CSA certified cULus Listed
PRODUCT TYPE	Locking receptacle

Product specifications

SPECIAL FEATURES	Corrosion resistant locking connector
TYPE	Locking receptacle
AMPERAGE RATING	15A
VOLTAGE RATING	277 V
CONTACT MATERIAL	Brass
APPLICATION	Industrial
DEVICE GRADE	Extra heavy-duty industrial specification grade
WIRING METHOD	Back and side
NUMBER OF WIRES	Grounding 3
NUMBER OF POLES	Two-pole
COLOR	Black
MATERIAL	Glass filled nylon
OPERATING TEMPERATURE	-40 to 115 °C (-40 to 239 °F)
ALLOWABLE WIRE SIZE	#14-10 AWG
NEMA CONFIGURATION	L7-15
DESIGN TYPE	Duplex
FACE/BODY MATERIAL	Glass filled nylon
RECEPTACLE TYPE	Locking

Resources

MULTIMEDIA

[Arrow Hart - Connecting Safety to Reliability since 1890](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - 4750](#)

[Industrial grade L7-15 locking devices spec sheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

